

RSM-16 PLC C SW 1CO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Digital output interface per-relay for electrical signal transmission between the PLC and the field.

- Electrical isolation using pluggable relays.
- Integrated LED status display.
- Screw or tension clamp connection.
- The relay switchover can be carried out by the PLC or manually by a relay.
- Two available versions: compact (RSS Relais) or standard (RSS Relais) .

General ordering data

Version	Interface, RSM PLC, 16 with switch, RSS, Screw connection
Order No.	1129030000
Type	RSM-16 PLC C SW 1CO S
GTIN (EAN)	4032248910465
Qty.	1 pc(s).

Creation date March 7, 2023 4:28:33 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

RSM-16 PLC C SW 1CO S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	85 mm	Depth (inches)	3.346 inch
Height	109 mm	Height (inches)	4.291 inch
Width	111 mm	Width (inches)	4.37 inch
Net weight	475 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	50 °C

General data

LED status display per relay	green	Fuse per relay	No
Switch	Yes (coil side)	LED status of the supply voltage	yellow
Power supply fuse	2.5 A		

Connection data

Connection (field side)	LL3R 5.08 mm	Connection on control side	Plug-in connector in acc. with IEC60603-13 / DIN41651
Connection supply	LL 5.08 mm	Number of poles (control side)	20-pole plug

Rating data

Mechanical service life	5 x 10 ⁶ switching cycles
-------------------------	--------------------------------------

Ratings data input

Input voltage	24 V DC ± 10%	Input current	13 mA
Power rating	0.36 W		

Ratings data output

Relay type	RSS	Type of output	Potential-free contact
Contact material	AgNi 90/10	Rated voltage	250 V AC
Max. AC continuous current	2.5 A	Minimum contact current	0.1 A
Minimum contact voltage	5 V		

Insulation coordinates (EN50178)

According to	DIN EN 50178	Rated input insulation voltage	< 50 V AC
Rated output insulation voltage	250 V AC	Overvoltage category input/input	II
Overvoltage category input/output	III	Overvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	≥ 5.5 mm
Clearance input/input	≥ 0.2 mm	Clearance output/output	≥ 1.17 mm

RSM-16 PLC C SW 1CO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Connection field**

Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Max. wire cross-section, AWG	AWG 12	Min. wire cross-section, AWG	AWG 26
Sleeve with plastic collar, max.	2.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Type of connection	Screw connection		

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	2.5 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	20201124 Technical change to RSM-816 PLC CSW 1CO SZ
Catalogues	Catalogues in PDF-format
Brochures	

RSM-16 PLC C SW 1CO S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

