

RS D8-I 4...20MA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

**Do not use product for
 new developments, Only
 remaining stock available**



D/A converters convert digital signals into analogue signals.
 They are used for converting 8-bit digital signals into standardised analogue current and voltage signals.
 D/A converters are very well suited for use in monitoring processes.

General ordering data

Version	DA converter, Input : 8-bit pulse, Output : 4-20 mA
Order No.	1169261001
Type	RS D8-I 4...20MA
GTIN (EAN)	4032248103928
Qty.	1 Stück
Delivery status	This article will no longer be available in the future.
Available until	2022-06-30

Erstellungs-Datum May 25, 2023 10:28:18 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

RS D8-I 4...20MA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	72 mm	Height (inches)	2.835 inch
Width	35 mm	Width (inches)	1.378 inch
Length	70 mm	Length (inches)	2.756 inch
Net weight	72 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	0 °C...50 °C
Operating temperature, min.	0 °C	Operating temperature, max.	50 °C

Input

Input resistance, voltage	50 kΩ per input	Number of inputs	8-bit (1-bit signed)
Rated input level	5...24 V DC = High, 0 V DC = Low, max. 30 V = High		

Output

Conversion time	≤ 30 μs	Number of outputs	1
Offset current	4 mA	Output current	4...20 mA (as source)
load impedance voltage	≤ 500 Ω		

General data

Accuracy	± 1 LSB	Current consumption	25 mA (plus output current)
Galvanic isolation	Without isolation	Input/Output	8 bit / analogue
Rail	TS 35, TS 32	Voltage supply	24 V DC

Insulation coordination

EMC standards	EN 61000-6	Galvanic isolation	Without isolation
---------------	------------	--------------------	-------------------

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-90	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20	ECLASS 12.0	27-21-01-20

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	7b5ffb72-271d-4c73-8b09-bd0aaee3697a

RS D8-I 4...20MA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[Declaration of Conformity](#)

Engineering Data

[WSCAD, EPLAN](#)

User Documentation

[IS RS 8BIT ADC DAC](#)
[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

RS D8-I 4...20MA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Electric symbol

