

CC 30/60 O4MM MC NE GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ClipCard, Device markers, 30 x 60 mm, With hole, green
Order No.	1158820000
Type	CC 30/60 O4MM MC NE GN
GTIN (EAN)	4032248947522
Qty.	30 pc(s).
compatible printer	2715590000 2438520000 2438510000
Alternative product	1934410000

Creation date May 4, 2023 5:21:59 PM CEST

CC 30/60 04MM MC NE GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	30 mm	Height (inches)	1.181 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	4.6 g		

Temperatures

Operating temperature range	-40...100 °C	Humidity	≤ 60 %
-----------------------------	--------------	----------	--------

General data

Application/manufacture	With hole	Colour	green
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	5	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Recommended industries	Machinery
UL 94 flammability rating	V-2	Width	60 mm

Device markers

Drill-hole diameter	4.2 mm	Halogen	No
Humidity	≤ 60 %		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format

Data sheet

CC 30/60 04MM MC NE GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

