

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 15 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

Version	Klippon TB MH (Terminal Box - Multi Hinge), Empty enclosure, stainless steel enclosure, Height: 400 mm, Width: 300 mm, Depth: 150 mm, Gland plates: Bottom, Material: Stainless steel 1.4301 (304), electropolished, silver
Order No.	1194910001
Type	KTB MH 403015 S2E1
GTIN (EAN)	4050118107128
Qty.	1 Stück

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	400 mm	Height (inches)	15.748 inch
Width	300 mm	Width (inches)	11.811 inch
Mounting dimension - height	247 mm	Mounting dimension - width	326 mm
Net weight	11,996.788 g		

Temperatures

Operating temperature	-60 °C...135 °C	Operating temperature, min.	-60 °C
Operating temperature, max.	135 °C	Note: room temperature (service)	Limited to IP66 protection when used in temperatures greater than 105 °C.

Cable glands, left

M12	29	M16	16
M20	13	M25	6
M32	5	M40	4
M50	3	M63	0
M75	0		

Cable glands, right

M12	29	M16	16
M20	13	M25	6
M32	5	M40	4
M50	3	M63	0
M75	0		

Cable glands, top/bottom

M12	23	M16	13
M20	11	M25	5
M32	4	M40	3
M50	3	M63	0
M75	0		

Certificate numbers enclosure

Approval conditions	ATEX, CCoE, DNV, EAC, IECEx, INMETRO, KC, NEPSI, CCC, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus	Attestation of Conformity No. (AoC)	DE PS261X 160309 001ISS03
Certificate No. (ATEX)	PTB11ATEX2019	Certificate No. (CCOE)	P461058_1
Certificate No. (IECEX)	IECEXPTB11.0071	Certificate No. (MARITREG)	21.50075.272
Certificate No. Electronic Box (NEPSI)	2020322303003289	Certificate No. UL 508A	E223801
Certificate No. UL Haz.Loc.	E223792	Certificate No. UL Ord.Loc.	E243298
Certificate No. UL Terminal Box	E223792	Certificate no. (INMETRO)	IEX17.0021
Certificate no. (cULus)	E243298	Certificate no. Terminal Box (INMETRO)	LMP 21.0017
Certificate no. empty enclosure (ECAS)	21-09-25241/ E21-09-053807	Declaration of Conformity No. (DoC LVD)	DE PS261X 160412 001ISS02

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technische Daten

info@weidmueller.com

www.weidmueller.com

Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore

4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet)

M6 hexagonal head screws 10 SW

7 J ATEX version, 10 J version standard

Yes

Stainless steel 1.4301 (304)

1.5 mm

3 mm

Number of lid screws

4

Operating temperature, max. 135 °C

Overall dimensions 411 x 351 x 165

Protection class (UL) Type 3, Type 4X, Type 12

Seal material Silicone

Surface finish

electropolished

General information

AF size	10 mm
Access opening: width	
	241 mm
Dimension of box	
	490x550x240
Flange plate	Yes
Gland plates	Bottom
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread
Lid attachment	4 hinges and M6 hex-head slotted screws SW10
Material thickness of cover	1.5 mm
Material thickness of flange	3 mm
Note: protection class	If used in temperature ranges above 105 °C, IP protection is limited to IP 66.
Opening angle lid	130 °
Operating temperature, min.	-60 °C
Position PE bolts	Enclosure side C
Protection degree	IP66, IP67
Standards	DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31
Torque for lid screws	2.5 Nm

Access opening: height	247 mm
Areas of use	
Enclosure attachment	
Flange plate mounting	
Impact resistance	
Lid	
Material	
Material thickness of enclosure	
Max. payload	48 kg
Number of lid screws	
Operating temperature, max.	
Overall dimensions	
Protection class (UL)	
Seal material	
Surface finish	

Housing earth

Earth, enclosure, internal	Welded-on M6 stainless-steel earth stud in enclosure body and lid.
----------------------------	--

horizontal assembly

WDU 10 / ZDU 10	2x19	WDU 16 / ZDU 16	2x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x39	WDU 35 / ZDU 35	1x11
WDU 4 / ZDU 4	3x32	WDU 6 / ZDU 6	2x24

vertical assembly

WDU 10 / ZDU 10	1x30	WDU 16 / ZDU 16	1x24
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x59	WDU 35 / ZDU 35	1x18
WDU 4 / ZDU 4	2x49	WDU 6 / ZDU 6	1x37

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmuller.com

www.weidmuller.com

Technische Daten

Classifications

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ECLASS 9.0	27-18-05-02
ECLASS 9.1	27-18-05-02	ECLASS 10.0	27-18-05-02
ECLASS 11.0	27-18-05-02	ECLASS 12.0	27-18-05-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd

Important note

Product information	Minimum order quantity (5 pieces)
---------------------	-----------------------------------

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E243298

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technische Daten

info@weidmueller.com

www.weidmueller.com

Downloads

Approval/Certificate/Document of Conformity

[C-DE.HB07.B.00089-Empty Enclosures and Ex. Terminal Box](#)
[C-DE.A154.B.00251.19 Ind. Terminal Box](#)
[CCC 2020322303002358 KTB Assembly Enclosure](#)
[CCC 2020322303002357 KTB Empty Enclosure](#)
[Attestation of Conformity - Klippon TB Empty Enclosures - AoC DE PS261X 160309 001ISS05 IEX17.0020U](#)
[IBEXU14ATEX1028U](#)
[IBEXU14ATEX1050](#)
[IECEXIBE14.0004U](#)
[IECEXIBE14.0013](#)
[TAE000013S](#)
[15.40073.250](#)
[GYJ14.1310X](#)
[IECEXPTB11.0071](#)
[PTB11ATEX2019](#)
[16-AV4BO-245X](#)
[P4610581_1](#)
[21-09-25241/E2 1-09-053807](#)
[EU Declaration of Conformity - Klippon TB Empty Enclosures - DoC DE PS261X 160412 001ISS03](#)

User Documentation

[Assembly guidelines - empty enclosures](#)

Catalogues

[Catalogues in PDF-format](#)

KTB MH 403015 S2E1

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Dimensioned drawing

