

**THM VIN 36/18 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

Version	THM, Device markers, 18 x 36 mm, silver
Order No.	<a href="#">1209010000</a>
Type	THM VIN 36/18 SI
GTIN (EAN)	4032248990108
Qty.	1 pc(s).

## THM VIN 36/18 SI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	18 mm	Height (inches)	0.709 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	344 g		

## Temperatures

Operating temperature range	-50...90 °C
-----------------------------	-------------

## General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	silver	Material	Vinyl film
Number of markers per combination	1 Label reel = Device markers	Number per roll	2,500
Operating temperature range	-50...90 °C	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Printing method	Thermal transfer
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	36 mm		

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>