

## IE-C5DD4UG0050MSSA20-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12-RJ45

### General ordering data

Version	Dragline cable, PROFINET, M12 D-code – IP 67 straight socket, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 5 m
Order No.	<a href="#">1211080050</a>
Type	IE-C5DD4UG0050MSSA20-E
GTIN (EAN)	4050118072723
Qty.	1 pc(s).

Creation date March 13, 2023 12:33:25 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## IE-C5DD4UG0050MSSA20-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	336 g		

## Temperatures

Storage temperature	-50 °C...70 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Installation temperature	-20 °C...60 °C		

## Cable specific standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## General standards

Certificate no. (cULus)	E316369
-------------------------	---------

## Standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/7 - 0.32 mm <sup>2</sup>
Diameter of inner sheathing	3.9 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PUR	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Shielding colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YH(ST)C11Y 2x2x0,75/1,5-100 LI VZN GN FRNC
Strands	7	Wire core insulation thickness	0.38 mm
Wire material	Stranded tin-plated copper wire		

## Electrical properties of cable

Capacity at 1 kHz	52 nF/km
Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 15 Ω at 1–100 MHz
Deviation	40 ns/100m
Loop resistance	120 Ω/km
Operating voltage (UL rating)	Operating voltage 600 V
Operating voltage (UL rating)	600 V undefined
Operating voltage, UL	600 V

Creation date March 13, 2023 12:33:25 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**IE-C5DD4UG0050MSSA20-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

Resistance differential	3 %
Signal propagation time	5.3 ns/m
Speed	180 m/min
Test voltage: wire-wire-shield	2000 V <sub>eff</sub> , 50 Hz, 1 min
Transfer impedance	20 mΩ/m at 10 MHz

**Mechanical and material properties of cable**

Abrasion resistance	very good	Acceleration	4 m/s <sup>2</sup>
Bending cycles	3 Mio	Fire propagation	No
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	7.5 x cable diameter	Pulling force	≤ 150 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1
Silicone-free	Yes	Speed	180 m/min
UV-resistant	Yes		

**Plug**

Plug left	M12, IP67, female contact, straight, plug, Plastic, shielded	Plug right	RJ45, IP20, male contact, straight, plug, Plastic, shielded
-----------	--	------------	---

**Plug, left**

Connector left	M12 D-code – IP 67 straight socket
----------------	------------------------------------

**Plug, right**

Connector right	RJ45 IP 20
-----------------	------------

**Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Creation date March 13, 2023 12:33:25 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

3

**IE-C5DD4UG0050MSSA20-E****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**Data sheet**


**IE-C5DD4UG0050MSSA20-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

**Drawings**

**Dimensioned drawing**



**Dimensioned drawing**



**Wiring diagram**

RJ45		M12
1	_____ gelb _____	1
3	_____ weiß _____	2
2	_____ orange _____	3
6	_____ blau _____	4