

CP M DM40


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Use our diode and redundancy modules to connect two power supplies and compensate for a device failing. In addition, our capacity module offers power reserves, guaranteeing purposeful and quick triggering of a circuit breaker, for example.

General ordering data

Version	Diode module
Order No.	1222220000
Type	CP M DM40
GTIN (EAN)	4050118005455
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31
Alternative product	2486100000

Creation date March 1, 2023 12:40:06 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

CP M DM40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	130 mm	Height (inches)	5.118 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	867 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	70 °C
Humidity	5...95 %, no condensation		

Input

DC input voltage range	18...30 V DC	Input current	2 x 20 A or 1 x 40 A
Rated input voltage	24 V DC	Wire connection method	Screw connection

Output

Continuous output current @ U _{Nominal}	48 A @ 45 °C, 45 A @ 55 °C, 30 A @ 70 °C	Nominal output current for U _{nom}	40 A @ 60 °C
Output current, max.	48 A	Output voltage, note	Voltage input - 0.7 V
Rated output voltage	24 V DC ± 1 %	Switching thresholds	21.6 V DC, relay is on for Power Good, 20.4 V DC, relay is off for Power Fail
Voltage monitoring	Yes, In both inputs	Wire connection method	Screw connection

General data

Degree of efficiency	> 97% @ 24 V Input voltage	Humidity	5...95 %, no condensation
Mounting position, installation notice	Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.	Operating temperature	-25 °C...70 °C
Protection degree	IP20		

EMC / shock / vibration

Interference immunity test acc. to	EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)	Noise emission in accordance with EN55032	Class B
Shock resistance IEC 60068-2-27	15 g In all directions	Vibration resistance IEC 60068-2-6	1 g according to EN 50178

Insulation coordination

Insulation voltage	0.5 kV _{Input / output - Box}	Pollution severity	2
Protection class	III, with no ground connection, for SELV		

Creation date March 1, 2023 12:40:06 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

2

CP M DM40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
------------------------------	-----------------	-----------------------------------	---------------------------

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , min.	2.5 mm ²	Conductor cross-section, rigid , max.	16 mm ²
Conductor cross-section, rigid , min.	0.5 mm ²	Wire connection cross section, flexible (input), max.	10 mm ²

Connection data (output)

Conductor cross-section, AWG/kcmil , max.	6	Conductor cross-section, AWG/kcmil , min.	22
Conductor cross-section, flexible , max.	10 mm ²	Conductor cross-section, flexible , min.	2.5 mm ²
Conductor cross-section, rigid , max.	16 mm ²	Conductor cross-section, rigid , min.	0.5 mm ²
Number of terminals	4 (3 +, 4 +, 3 -, 4 -)		

Signalling

Floating contact	Yes
------------------	-----

Approbations

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ECLASS 9.0	27-04-07-01
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-90	ECLASS 12.0	27-04-07-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	c9dca554-f123-4c2f-a680-5a7631aa9527

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476

CP M DM40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	DE_PA5200_160512_001.pdf
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format
Brochures	
