

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found in process or power generation industries. The Klippon® TB FS enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB FS enclosure range features the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet

### General ordering data

|            |  |
|------------|--|
| Version    | Klippon TB FS (Terminal Box - Fixing Screw), Empty enclosure, stainless steel enclosure, Height: 762 mm, Width: 508 mm, Depth: 200 mm, Gland plates: Bottom, left, right, Material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">1196580000</a>   |
| Type       | KTB FS 765020 S4E3   |
| GTIN (EAN) | 4032248979516  |
| Qty.       | 1 Stück  |

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|                             |          |                            |            |
|-----------------------------|----------|----------------------------|------------|
| Depth                       | 200 mm   | Depth (inches)             | 7.874 inch |
| Height                      | 762 mm   | Height (inches)            | 30 inch    |
| Width                       | 508 mm   | Width (inches)             | 20 inch    |
| Mounting dimension - height | 508 mm   | Mounting dimension - width | 564 mm     |
| Net weight                  | 19,080 g |                            |            |

### Temperatures

|                             |                 |                                  |   |
|-----------------------------|-----------------|----------------------------------|---|
| Operating temperature       | -60 °C...135 °C | Operating temperature, min.      | -60 °C  |
| Operating temperature, max. | 135 °C          | Note: room temperature (service) | Limited to IP66 protection when used in temperatures greater than 105 °C. |

### Cable glands, left

|     |    |     |    |
|-----|----|-----|----|
| M12 | 96 | M16 | 64 |
| M20 | 40 | M25 | 34 |
| M32 | 18 | M40 | 14 |
| M50 | 6  | M63 | 6  |
| M75 | 4  |     |    |

### Cable glands, right

|     |    |     |    |
|-----|----|-----|----|
| M12 | 96 | M16 | 64 |
| M20 | 40 | M25 | 34 |
| M32 | 18 | M40 | 14 |
| M50 | 6  | M63 | 6  |
| M75 | 4  |     |    |

### Cable glands, top/bottom

|     |    |     |    |
|-----|----|-----|----|
| M12 | 70 | M16 | 48 |
| M20 | 32 | M25 | 26 |
| M32 | 14 | M40 | 12 |
| M50 | 5  | M63 | 4  |
| M75 | 3  |     |    |

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Certificate numbers enclosure

|   |   |   |   |
|---|---|---|---|
| Approval conditions                     | ATEX, CCoE, DNV, EAC, IECEx, INMETRO, KC, NEPSI, CCC, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus | Attestation of Conformatiy No. (AoC)      | DE PS261X 160309 001ISS03                   |
| Certificate No. (ATEX)                  | KEMA10ATEX0046U   | Certificate No. (EAC)                     | C-DE.HB07.B.00089-20                        |
| Certificate No. (IECEX)                 | IECEXKEM10.0017   | Certificate No. Electronic Box (NEPSI)    | 2020322303003289                            |
| Certificate No. UL 508A                 | E223801   | Certificate No. UL Haz.Loc.               | E223792                                     |
| Certificate No. UL Ord.Loc.             | E243298   | Certificate No. UL Terminal Box           | E223792                                     |
| Certificate no. (INMETRO)               | IEX13.0007  | Certificate no. (cULus)                   | E256877                                     |
| Certificate no. Terminal Box (AEx)      | E223792   | Certificate no. Terminal Box (ATEX)       | IBExU14ATEX1050                             |
| Certificate no. Terminal Box (EAC)      | C-DE.HB07.B.00089/20 Ex Terminal Box; C-DE.AQ54.B.00251/19 Ind. Terminal Box                            | Certificate no. Terminal Box (IECEX)      | IECEXIBE14.0013                             |
| Certificate no. Terminal Box (INMETRO)  | LMP 21.0017   | Certificate no. Terminal Box (KOSHA)      | 16-AV4BO-0245X                              |
| Certificate no. empty enclosure (ATEX)  | IBExU14ATEX1028 U   | Certificate no. empty enclosure (ECAS)    | <b>21-09-25241/</b><br><b>E21-09-053807</b> |
| Certificate no. empty enclosure (IECEX) | IECEX IBE 14.0004U  | Certificate no. empty enclosure (INMETRO) | IEx 17.0020U                                |
| Certificate no., empty enclosure (EAC)  | C-DE.HB07.B.00089/20  | Declaration of Conformatiy No. (DoC LVD)  | DE PS261X 160412 001ISS02                   |

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### General information

|                                 |  |                              |   |
|---------------------------------|--|------------------------------|---|
| AF size                         | 10 mm  | Access opening: height       | 710 mm  |
| Access opening: width           |  | Areas of use                 | Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore |
| Dimension of box                | 456 mm   | Enclosure attachment         | 4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet)               |
| Flange plate                    | 690x920x290  | Flange plate mounting        | M6 hexagonal head screws 10 SW  |
| Gland plates                    | Yes  | Impact resistance            | 7 J ATEX version, 10 J version standard   |
| Integral fixing                 | Bottom, left, right  | Lid attachment               | M6 hex-head slotted screws SW10   |
| Material                        | 4, 6 or 9 stud bolts M6 inner (female) thread  | Material thickness of cover  | 1.5 mm  |
| Material thickness of enclosure | Stainless steel 1.4404 (316L)  | Material thickness of flange | 3 mm  |
| Max. payload                    | 1.5 mm   | Note: protection class       | If used in temperature ranges above 105 °C, IP protection is limited to IP 66.                    |
| Number of lid screws            | 155 kg   | Operating temperature, max.  | 135 °C  |
| Operating temperature, min.     | 8  | Overall dimensions           | 773 x 589 x 208.5   |
| Position PE bolts               | -60 °C   | Protection class (UL)        | Type 3, Type 4X, Type 12  |
| Protection degree               | Enclosure side C   | Seal material                | Silicone  |
| Standards                       | IP66, IP67   | Surface finish               | electropolished   |
| Torque for lid screws           | DIN EN 62208 - Empty enclosure standard, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31 |                              |   |

### Housing earth

|                            |   |
|----------------------------|---|
| Earth, enclosure, internal | Welded-on M6 stainless-steel earth stud in enclosure body and lid., Continuous M10 earth stud in body enclosure |
|----------------------------|---|

### horizontal assembly

|                             |      |                 |      |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10             | 5x42 | WDU 16 / ZDU 16 | 4x35 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 7x82 | WDU 35 / ZDU 35 | 3x26 |
| WDU 4 / ZDU 4               | 6x69 | WDU 6 / ZDU 6   | 5x52 |

### vertical assembly

|                             |       |                 |      |
|-----------------------------|-------|-----------------|------|
| WDU 10 / ZDU 10             | 3x67  | WDU 16 / ZDU 16 | 2x56 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 4x132 | WDU 35 / ZDU 35 | 2x42 |
| WDU 4 / ZDU 4               | 4x111 | WDU 6 / ZDU 6   | 3x83 |

Erstellungs-Datum May 22, 2023 3:47:25 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002503    | ETIM 7.0    | EC002503    |
| ETIM 8.0    | EC002503    | ECLASS 9.0  | 27-18-05-02 |
| ECLASS 9.1  | 27-18-05-02 | ECLASS 10.0 | 27-18-05-02 |
| ECLASS 11.0 | 27-18-05-02 | ECLASS 12.0 | 27-18-05-02 |

### Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd |

### Approvals

Approvals



|                         |            |
|-------------------------|------------|
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E256877    |

## KTB FS 765020 S4E3

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">C-DE.HB07.B.00089-Empty Enclosures and Ex. Terminal Box</a><br><a href="#">C-DE.AJ54.B.00251.19 Ind. Terminal Box</a><br><a href="#">CCC 2020322303002358 KTB Assembly Enclosure</a><br><a href="#">CCC 2020322303002357 KTB Empty Enclosure</a><br><a href="#">Attestation of Conformity - Klippon TB Empty Enclosures - AoC DE PS261X 160309 001ISS05 IEX17.0020U</a><br><a href="#">IBEXU14ATEX1028U</a><br><a href="#">IBEXU14ATEX1050</a><br><a href="#">IECEXIBE14.0004U</a><br><a href="#">IECEXIBE14.0013</a><br><a href="#">TAE000013S</a><br><a href="#">15.40073.250</a><br><a href="#">RUC-DE.MIO62.B.04799</a><br><a href="#">GYJ14.1310X</a><br><a href="#">IECEXPTB11.0071</a><br><a href="#">PTB11ATEX2019</a><br><a href="#">16-AV4BO-245X</a><br><a href="#">P4610581_1</a><br><a href="#">21-09-25241/E21-09-053807</a><br><a href="#">LMP 21.0017 - CAIXA DE JUNÇÃO KLIPPON TB - KTB MH QL FS</a><br><a href="#">EU Declaration of Conformity - Klippon TB Empty Enclosures - DoC DE PS261X 160412 001ISS03</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| Engineering Data                            | <a href="#">WSCAD, EPLAN</a>  |
| Tender specification                        | <a href="#">Klippon TB FS 765020 S4E3_1196580000_DE</a><br><a href="#">Klippon TB FS 765020 S4E3_1196580000_EN</a><br><a href="#">Klippon TB FS 765020 S4E3_1196580000_NL</a>   |
| User Documentation                          | <a href="#">Assembly guidelines - empty enclosures</a>  |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>  |
| Brochures                                   | <a href="#">MB OVERV. PROCESS WD DE</a><br><a href="#">MB KLIPPON ENCL.TECN EN</a><br><a href="#">MB PROCESS EN</a><br><a href="#">FL WIND 2012 EN</a><br><a href="#">FL APPL PROCESS EN</a><br><a href="#">FL SHIPBUILDING 2016 EN</a><br><a href="#">FL RAILWAY 2014 EN</a><br><a href="#">PI KLIPPON TB MH QL EN</a>   |

**Dimensioned drawing**

