

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB QL enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB QL enclosure series features the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Quick-locking cover, comes with a slot as standard
- Improved temperature performance
- IP66 protection
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

| | |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version | Klippon TB QL (Terminal Box - Quarter Lock), Empty enclosure, stainless steel enclosure, Height: 400 mm, Width: 300 mm, Depth: 150 mm, Material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No. | 1200220000 |
| Type | KTB QL 403015 S4E0 |
| GTIN (EAN) | 4032248983018 |
| Qty. | 1 Stück |
| Available until | 2015-11-24 |

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 150 mm | Depth (inches) | 5.905 inch |
| Height | 400 mm | Height (inches) | 15.748 inch |
| Width | 300 mm | Width (inches) | 11.811 inch |
| Mounting dimension - height | 247 mm | Mounting dimension - width | 326 mm |
| Net weight | 6,000 g | | |

Temperatures

| | | | |
|-----------------------------|-----------------|----------------------------------|---------------------------------------------------------------------------|
| Operating temperature | -60 °C...135 °C | Operating temperature, min. | -60 °C |
| Operating temperature, max. | 135 °C | Note: room temperature (service) | Limited to IP66 protection when used in temperatures greater than 105 °C. |

Cable glands, left

| | | | |
|-----|----|-----|----|
| M12 | 29 | M16 | 16 |
| M20 | 13 | M25 | 6 |
| M32 | 5 | M40 | 4 |
| M50 | 3 | M63 | 0 |
| M75 | 0 | | |

Cable glands, right

| | | | |
|-----|----|-----|----|
| M12 | 29 | M16 | 16 |
| M20 | 13 | M25 | 6 |
| M32 | 5 | M40 | 4 |
| M50 | 3 | M63 | 0 |
| M75 | 0 | | |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M12 | 23 | M16 | 13 |
| M20 | 11 | M25 | 5 |
| M32 | 4 | M40 | 3 |
| M50 | 3 | M63 | 0 |
| M75 | 0 | | |

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Certificate numbers enclosure

| | | | |
|-------------------------------------------|---------------------------------------------------------------------------------------------------------|-----------------------------------------|------------------------------------------------------------------------------|
| Approval conditions | ATEX, CCoE, DNV, EAC, IECEx, INMETRO, KC, NEPSI, CCC, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus | Attestation of Conformatiy No. (AoC) | DE PS261X 160309 001ISS03 |
| Certificate No. (ATEX) | KEMA10ATEX0046U | Certificate No. (CCOE) | P461058_1 |
| Certificate No. (EAC) | C-DE.HB07.B.00089-20 | Certificate No. (IECEX) | IECEXKEM10.0015U |
| Certificate No. Electronic Box (NEPSI) | 2020322303003289 | Certificate No. UL 508A | E223801 |
| Certificate No. UL Haz.Loc. | E223792 | Certificate No. UL Ord.Loc. | E243298 |
| Certificate No. UL Terminal Box | E223792 | Certificate no. (INMETRO) | IEX13.0006U |
| Certificate no. (cULus) | E243298 | Certificate no. Terminal Box (AEx) | E223792 |
| Certificate no. Terminal Box (ATEX) | IBExU14ATEX1050 | Certificate no. Terminal Box (EAC) | C-DE.HB07.B.00089/20 Ex Terminal Box; C-DE.A154.B.00251/19 Ind. Terminal Box |
| Certificate no. Terminal Box (IECEX) | IECEXIBE14.0013 | Certificate no. Terminal Box (INMETRO) | LMP 21.0017 |
| Certificate no. Terminal Box (KOSHA) | 16-AV4BO-0245X | Certificate no. empty enclosure (ATEX) | IBExU14ATEX1028 U |
| Certificate no. empty enclosure (ECAS) | 21-09-25241/ E21-09-053807 | Certificate no. empty enclosure (IECEX) | IECEX IBE 14.0004U |
| Certificate no. empty enclosure (INMETRO) | IEx 17.0020U | Certificate no., empty enclosure (EAC) | C-DE.HB07.B.00089/20 |
| Declaration of Conformatiy No. (DoC LVD) | DE PS261X 160412 001ISS02 | | |

General information

| | | | |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|--------------------------------------------------------------------------------|
| Access opening: height | 347 mm | Access opening: width | 241 mm |
| Areas of use | Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore | Dimension of box | 490x550x240 |
| Enclosure attachment | 4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet) | Flange plate | No |
| Impact resistance | 7 J ATEX version, 10 J version standard | Integral fixing | 4, 6 or 9 stud bolts M6 inner (female) thread |
| Lid attachment | Quarter-turn fastener with slotted insert | Material | Stainless steel 1.4404 (316L) |
| Material thickness of cover | 1.5 mm | Material thickness of enclosure | 1.5 mm |
| Max. payload | 48 kg | Note: protection class | If used in temperature ranges above 105 °C, IP protection is limited to IP 66. |
| Opening angle lid | 130 ° | Operating temperature, max. | 135 °C |
| Operating temperature, min. | -60 °C | Overall dimensions | 400 x 351 x 160 |
| Position PE bolts | Enclosure side C | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Protection degree | IP66 | Seal material | Silicone |
| Standards | DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31 | Surface finish | electropolished |

Erstellungs-Datum May 22, 2023 3:56:02 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Housing earth

Earth, enclosure, internal Welded-on M6 stainless-steel earth stud in enclosure body and lid.

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 2x21 | WDU 16 / ZDU 16 | 2x18 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 3x42 | WDU 35 / ZDU 35 | 1x13 |
| WDU 4 / ZDU 4 | 3x35 | WDU 6 / ZDU 6 | 2x26 |

vertical assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 1x32 | WDU 16 / ZDU 16 | 1x26 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x62 | WDU 35 / ZDU 35 | 1x20 |
| WDU 4 / ZDU 4 | 2x52 | WDU 6 / ZDU 6 | 1x39 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002503 | ETIM 7.0 | EC002503 |
| ETIM 8.0 | EC002503 | ECLASS 9.0 | 27-18-05-02 |
| ECLASS 9.1 | 27-18-05-02 | ECLASS 10.0 | 27-18-05-02 |
| ECLASS 11.0 | 27-18-05-02 | ECLASS 12.0 | 27-18-05-02 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E243298 |

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Downloads

| | |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | C-DE.HB07.B.00089-Empty Enclosures and Ex. Terminal Box C-DE.A154.B.00251.19 Ind. Terminal Box CCC 2020322303002358 KTB Assembly Enclosure CCC 2020322303002357 KTB Empty Enclosure Attestation of Conformity - Klippon TB Empty Enclosures - AoC DE PS261X 160309 001ISS05 IEX17.0020U IBEXU14ATEX1028U IBEXU14ATEX1050 IECEXIBE14.0004U IECEXIBE14.0013 TAE000013S 15.40073.250 RUC-DE.MIO62.B.04799 GYJ14.1310X IECEXPTB11.0071 PTB11ATEX2019 16-AV4BO-245X P4610581_1 21-09-25241/E21-09-053807 LMP 21.0017 - CAIXA DE JUNÇÃO KLIPPON TB - KTB MH QL FS EU Declaration of Conformity - Klippon TB Empty Enclosures - DoC DE PS261X 160412 001ISS03 DoM Railway applications - Fire protection on railway vehicles |
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Tender specification | Klippon TB QL 403015 S4E0_1200220000_DE Klippon TB QL 403015 S4E0_1200220000_EN Klippon TB QL 403015 S4E0_1200220000_NL |
| User Documentation | Assembly guidelines - empty enclosures |
| Catalogues | Catalogues in PDF-format |
| Brochures | MB OVERV. PROCESS WD DE MB KLIPPON ENCL.TECN EN MB PROCESS EN FL WIND 2012 EN FL APPL PROCESS EN FL SHIPBUILDING 2016 EN FL RAILWAY 2014 EN PI KLIPPON TB MH QL EN |

KTB QL 403015 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

