

IE-CDR-V14MSCPOF/VAPM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Delivery incl. dust caps

FreeCon Active PROFINET repeater for PushPull Var. 14
plug-in connectors according to IEC 61076-3-117 and
PushPull Power according to the PROFINET specification

General ordering data

Version	POF repeater, FreeCon, IP65
Order No.	1253240000
Type	IE-CDR-V14MSCPOF/VAPM-C
GTIN (EAN)	4050118045833
Qty.	1 Stück
Alternative product	2455360000

Erstellungs-Datum May 30, 2023 11:32:05 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

IE-CDR-V14MSCPOF/VAPM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	53 mm	Depth (inches)	2.087 inch
Width	100 mm	Width (inches)	3.937 inch
Length	130.4 mm	Length (inches)	5.134 inch
Net weight	725.8 g		

Temperatures

Operating temperature	-20 °C...55 °C	Operating temperature, min.	-20 °C
Operating temperature, max.	55 °C		

General data

Data interface	PROFINET PushPull SCRJ POF (V14)	Housing main material	Aluminium profile, Cover: die-cast zinc, painted
Plugging cycles	≥ 100	Power interface	PROFINET PushPull Power
Protection degree	IP65	UL 94 flammability rating	V-0
Wiring	PROFINET		

Electrical properties

Baud rate	100 MB	Current consumption	200 mA typical
LED indicator	FO1: port active, FO2: port active, SF: general error, BF: bus error, US1: voltage 1 (electronics), US2: voltage 2	Operating voltage	24 V DC
Operational voltage range	18...30 V DC	Protocol	PROFINET IRT

General standards

Certificate no. (cULus)	E141197	Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
Network standard	IEC 61158, IEC 61784		

Classifications

ETIM 6.0	EC000732	ETIM 7.0	EC000732
ETIM 8.0	EC000732	ECLASS 9.0	19-17-02-06
ECLASS 9.1	19-17-01-25	ECLASS 10.0	19-17-02-06
ECLASS 11.0	19-17-02-06	ECLASS 12.0	19-17-02-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

IE-CDR-V14MSCPOF/VAPM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	PNO_Zertifikat_1253240000.pdf
Engineering Data	CAD data – STEP
Software	Firmware – WM_FCA_PIR_POF_V_1_05_01.zip Device description – GSDML-V225-Weidmuller-FCAPIRPOF-20110913.zip Runtime Software – CFG configurator - Weidmueller_FreeCon_08042011
User Documentation	Manual EN MAN IE GUIDE DE MAN IE GUIDE EN Firmware update manual Manual DE
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-CDR-V14MSCPOF/VAPM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Dimensioned drawing



Wiring diagram

