

**SPW ECO 3CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Relay sockets for the D-SERIES DRW/DRH relays

- Up to 3 CO contacts
- Screw connection

**General ordering data**

Version	D-SERIES DRW / DRH, Relay socket, Number of contacts: 3, CO contact, Continuous current: 16 A, Screw connection
Order No.	<a href="#">1220250000</a>
Type	SPW ECO 3CO
GTIN (EAN)	4032248100101
Qty.	10 pc(s).

Creation date March 1, 2023 2:13:59 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## SPW ECO 3CO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	31 mm	Depth (inches)	1.22 inch
Height	92.1 mm	Height (inches)	3.626 inch
Width	38.7 mm	Width (inches)	1.524 inch
Net weight	64.1 g		

### Temperatures

Storage temperature	-40 °C...60 °C	Operating temperature	-40 °C...60 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	60 °C
Humidity	35...85 % rel. humidity, no condensation		

### Rated data UL

Certificate No. (cURus)	E312083
-------------------------	---------

### Load side

Rated switching voltage	500 V AC	Continuous current	16 A
Max. switching voltage, AC	500 V	Contact type	3 CO contact

### General data

Rail	TS 35		
Colour	black		
UL94 flammability rating component	Component	Housing	
	UL94 flammability rating	V-2	
	Component	Mounting foot	
	UL94 flammability rating	HB	
	Component	Retaining clip	
	UL94 flammability rating	HB	

### Insulation coordination

Rated voltage	500 V	Pollution severity	2
Surge voltage category	II	Insulating material group	IIIb
Dielectric strength for control side - load side	4 kV <sub>eff</sub> / 1 min	Dielectric strength of neighbouring contacts	4 kV <sub>eff</sub> / 1 min
Impulse withstand voltage	7.3 kV (1.2/50 µs)	Protection degree	IP10

### Further details of approvals / standards

Certificate No. (cURus)	E312083
-------------------------	---------

## SPW ECO 3C0

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Connection data

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Tightening torque, min.	0.5 Nm	Tightening torque, max.	1.2 Nm
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	4 mm <sup>2</sup>
Wire cross-section, solid, min.	0.5 mm <sup>2</sup>	Wire cross-section, solid, max.	4 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	4 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	1.5 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm <sup>2</sup>
Wire connection	M4 forked cable lug (insulated)	Blade size	Gr. PH2

### Classifications

ETIM 6.0	EC001456	ETIM 7.0	EC001456
ETIM 8.0	EC001456	ECLASS 9.0	27-37-16-03
ECLASS 9.1	27-37-16-03	ECLASS 10.0	27-37-16-03
ECLASS 11.0	27-37-16-03	ECLASS 12.0	27-37-16-03

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Important note

Product information	For this socket, a cross connection is not available. For this socket, markers are not available.
---------------------	--

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E312083

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date March 1, 2023 2:13:59 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

3


**SPW ECO 3C0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Wiring diagram**



**Graph**



Dimensional drawing

**Dimensional drawing**