

KTB GP 453815 AB S4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

| | |
|------------|---|
| Version | Klippon TB (Terminal Box), flange plate, straight, Height: 376 mm, Width: 117 mm, Depth: 3 mm, Gland plates: top, Bottom, Material: Stainless steel 1.4404, electropolished, silver |
| Order No. | 1281070000 |
| Type | KTB GP 453815 AB S4 |
| GTIN (EAN) | 4050118071672 |
| Qty. | 1 Stück |

Erstellungs-Datum May 30, 2023 11:37:55 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

KTB GP 453815 AB S4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 3 mm | Depth (inches) | 0.118 inch |
| Height | 376 mm | Height (inches) | 14.803 inch |
| Width | 117 mm | Width (inches) | 4.606 inch |
| Net weight | 1,000 g | | |

General information

| | | | |
|-----------------------|--------------------------|--------------------|-----------------|
| Gland plates | top, Bottom | Integral fixing | Screwed |
| Material | Stainless steel 1.4404 | Material thickness | 3 mm |
| Protection class (UL) | Type 3, Type 4X, Type 12 | Surface finish | electropolished |

General information on accessories

| | | | |
|----------------|------------------------|--------------------|------|
| Material | Stainless steel 1.4404 | Material thickness | 3 mm |
| Surface finish | electropolished | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000211 | ETIM 7.0 | EC000211 |
| ETIM 8.0 | EC000211 | ECLASS 9.0 | 27-14-24-21 |
| ECLASS 9.1 | 27-18-92-90 | ECLASS 10.0 | 27-14-24-21 |
| ECLASS 11.0 | 27-14-24-21 | ECLASS 12.0 | 27-14-24-21 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |