

CC 15/49 K MC NE RT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|---------------------|--|
| Version | ClipCard, Device markers, 15 x 49 mm, red |
| Order No. | 1288380000 |
| Type | CC 15/49 K MC NE RT |
| GTIN (EAN) | 4050118079760 |
| Qty. | 40 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |
| Alternative product | 1877230000 |

Erstellungs-Datum May 16, 2023 11:10:35 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CC 15/49 K MC NE RT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 1.2 mm | Depth (inches) | 0.047 inch |
| Height | 15 mm | Height (inches) | 0.591 inch |
| Width | 49 mm | Width (inches) | 1.929 inch |
| Net weight | 3.05 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|----------------------------|-----------------------------------|------------------------------|
| Adhesive | Double-sided adhesive tape | Colour | red |
| Halogen | No | Material | Polyamide 66 |
| Material colour according to resistance code | 2 | Number of markers per combination | 1 MultiCard = Device markers |
| Operating temperature range | -40...60 °C | Operating temperature range, max. | 60 °C |
| Operating temperature range, min. | -40 °C | Recommended industries | Machinery |
| UL 94 flammability rating | V-2 | Version | Self-adhesive |
| Width | 49 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Product Change Notification | Technical change - DE Technical change - EN |
| Catalogues | Catalogues in PDF-format |

CC 15/49 K MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

