

SM 19/42 K MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 19 x 42 mm, To customer specification
Order No.	1248560000
Type	SM 19/42 K MC SDR
GTIN (EAN)	4050118038873
Qty.	8 pc(s).
compatible printer	2715590000 2438520000 2438510000

SM 19/42 K MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	19 mm	Height (inches)	0.748 inch
Width	42 mm	Width (inches)	1.654 inch
Net weight	2.375 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

General data

Colour	To customer specification	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...60 °C	Operating temperature range, max.	60 °C
Operating temperature range, min.	-40 °C	Printed characters	Based on customer requirements (Please send M-Print PRO file)
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	42 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format

Data sheet

SM 19/42 K MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

