

SAIB-M16-8/9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M16 round plug-in connectors can transmit large amounts of power and have set the standard in the market for many years. The solder connection provides high contact density on a small area. With this technology the stripped conductor is soldered to the contacts, producing good electrical conductivity.

General ordering data

| | |
|------------|--|
| Version | Field attachable connector, M16, Female socket, straight |
| Order No. | 1304450000 |
| Type | SAIB-M16-8/9 |
| GTIN (EAN) | 4050118103373 |
| Qty. | 1 pc(s). |

Creation date March 7, 2023 8:24:43 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

SAIB-M16-8/9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 33 g

Technical data customisable plug-in connectors

| | | | |
|--------------------------------|---|--------------------------------|----------------------|
| Cable diameter | 6...8 mm (PG9) | Cable diameter, max. | 8 mm |
| Cable diameter, min. | 6 mm | Coding | none |
| Conductor cross-section, max. | 0.75 mm ² | Conductor cross-section, min. | 0.14 mm ² |
| Connection cross-section, max. | 0.25 mm ² | Connection cross-section, min. | 0.14 mm ² |
| Contact surface | Ag (silver) | Housing main material | PA |
| Insulation strength | 10 ⁸ Ω | Number of poles | 8 |
| Plugging cycles | ≥ 500 | Pollution severity | 3 |
| Protection degree | IP40 | Rated current | 5 A |
| Rated current | 7 A (2-pole) / 6 A (4- and 5-pole) / 5 A (6-, 7- and 8-pole) / 3 A (12- and 16-pole) | Rated voltage | 60 V |
| Rated voltage | 250 V (2-, 4-, 5- and 6-pole) / 125 V (7-pole) / 60 V (8- and 12-pole) / 30 V (16-pole) | Shield connection | No |
| Temperature range of housing | -40 ... +85 °C | Threaded ring material | Diecast zinc |
| Type of connection | Solder connection | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002635 | ETIM 7.0 | EC002635 |
| ETIM 8.0 | EC002635 | ECLASS 9.0 | 27-44-01-02 |
| ECLASS 9.1 | 27-44-01-03 | ECLASS 10.0 | 27-44-01-02 |
| ECLASS 11.0 | 27-44-01-02 | ECLASS 12.0 | 27-44-01-16 |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

Approvals



ROHS Conform

Downloads

| | |
|--------------------|--|
| User Documentation | Manual |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |