

## SM 18/9.5 K MC NE GR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	SwitchMark, Device markers, 9.5 x 18 mm, grey
Order No.	<a href="#">1248610000</a>
Type	SM 18/9.5 K MC NE GR
GTIN (EAN)	4050118038675
Qty.	200 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

## SM 18/9.5 K MC NE GR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	9.5 mm	Height (inches)	0.374 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	0.57 g		

## Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

## General data

Adhesive	Double-sided adhesive tape	Colour	grey
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	8	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...60 °C	Operating temperature range, max.	60 °C
Operating temperature range, min.	-40 °C	UL 94 flammability rating	V-2
Version	Self-adhesive	Width	18 mm

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**SM 18/9.5 K MC NE GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**



Similar to illustration

