

IE-C5ES8VG0600A40A40-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 60 m
Order No.	1318000000
Type	IE-C5ES8VG0600A40A40-E
GTIN (EAN)	4050118123647
Qty.	1 pc(s).
Available until	2012-12-31

Creation date March 13, 2023 1:24:36 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-C5ES8VG0600A40A40-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	60 m	Length (inches)	2,362.205 inch
Net weight	2,075 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	0 °C...50 °C		

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm ²
Diameter of wire pair	2 mm	Insulation	PE
Insulation cross-section	1 mm	Material sheath	PVC
Number of wires	8	Overlap of shielding braid	65 %
Sheath diameter, max.	6.1 mm	Sheath diameter, min.	5.7 mm
Sheathing colour	green (RAL 6018)	Shielding	SF/UTP
Shielding braid thickness	0.1 mm	Strands	7
Wire core insulation thickness	0.25 mm	Wire material	Stranded tin-plated copper wire

Electrical properties of cable

Capacity at 1 kHz	47 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 5 Ω at 100MHz	Deviation	25 ns/100m
Loop resistance	290 Ω/km	Resistance differential	3 %
Signal propagation time	4.85 ns/m	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	10 mΩ/m at 10 MHz		

Mechanical and material properties of cable

Abrasion resistance	good	Fire propagation	No
Halogen	Yes	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Resistance to spread of flame	in accordance with IEC 60332-1

Plug

Plug left	RJ45, IP20, male contact, straight, Plastic, shielded	Plug right	RJ45, IP20, male contact, straight, Plastic, shielded
-----------	---	------------	---

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

IE-C5ES8VG0600A40A40-E**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN