

**IE-FM6C2UE0300MSD1SD1X****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

**General ordering data**

Version	Dragline cable, SC IP 67 bayonet V01 metal, SC IP 67 bayonet V01 metal, 62.5 µm, PUR, 300 m
Order No.	<a href="#">1318013000</a>
Type	IE-FM6C2UE0300MSD1SD1X
GTIN (EAN)	4050118170726
Qty.	1 Stück
Available until	2013-12-06

**IE-FM6C2UE0300MSD1SD1X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	300 m	Length (inches)	11.811023 inch
Net weight	0.01 g		

**Temperatures**

Storage temperature	-55 °C...85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Installation temperature	-55 °C...60 °C		

**Cable structure**

Cable layout	Break-out dragline	Core diameter	62.5 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	7.5–8 mm	Sheathing colour	black

**Mechanical and material properties of cable**

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	70 mm		

**Plug**

Plug	Cable side	left
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	V1 Bayonett
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	No
	Cable side	right
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	V1 Bayonett
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	No

Plug left	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
Plug right	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded

**Plug, left**

Connector left	SC IP 67 bayonet V01 metal	Plug left	SC, IP67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
----------------	----------------------------	-----------	---

**IE-FM6C2UE0300MSD1SD1X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

**Technische Daten**

**Plug, right**

Connector right	SC IP 67 bayonet V01 metal	Plug right	www.weidmueller.com	SC IP 67, male contact, straight, V1 Bayonett, plug, Zinc diecast, unshielded
-----------------	----------------------------	------------	---------------------	---

**Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-FM6C2UE0300MSD1SD1X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Detailed drawing**

