

**PAC-UNIV-HE20-F-1M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Pre-assembled cable, PAC   |
| Order No.  | <a href="#">1349790010</a> |
| Type       | PAC-UNIV-HE20-F-1M         |
| GTIN (EAN) | 4032248161003              |
| Qty.       | 1 pc(s).                   |

**PAC-UNIV-HE20-F-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 80 g

**Temperatures**

|                             |             |                             |             |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature         | -10...60 °C | Operating temperature       | -10...50 °C |
| Operating temperature, min. | -10 °C      | Operating temperature, max. | 50 °C       |

**General Data**

|                    |   |                       |                                 |
|--------------------|---|-----------------------|---------------------------------|
| Cable              | Cable LiYY                                  | Cable length          | 1 m                             |
| Connector PLC side | H0.14/10 (FERRULES<br>0.14mm <sup>2</sup> ) | Interface connector   | FLAT CABLE CONECTOR<br>HE10 20P |
| Material           | PVC   | Number of poles, min. | 20-pole                         |
| Outer diameter     | 8.6 ± 1 mm                                  | Suitable for          | Digital signals                 |
| Wire cross-section | 0.14 mm <sup>2</sup>                        |                       |                                 |

**Electrical Data**

|                        |                     |  |           |
|------------------------|---------------------|--|-----------|
| Capacity wire / shield | 300 pF/m            | Capacity wire / wires                          | 300 pF/m  |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path,<br>max. | 1 A       |
| Rated voltage          | ≤ 60 V DC ≤ 25 V AC | Resistance                                     | ≤ 150mΩ/m |
| Total current, max.    | 3 A                 |  |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

**Approvals**

Approvals



ROHS Conform

**Downloads**

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">Colours chart</a>            |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |
| Brochures          |  |