

## PAC-UNIV-D9F-F-0M5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |   |
|------------|---|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 7,8 ± 1 mm |
| Order No.  | <a href="#">1350470005</a>                        |
| Type       | PAC-UNIV-D9F-F-0M5                                |
| GTIN (EAN) | 4032248254521                                     |
| Qty.       | 1 pc(s).  |

Creation date March 17, 2023 11:19:17 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## PAC-UNIV-D9F-F-0M5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 95.5 g

### Temperatures

|                             |             |                             |             |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature         | -10...60 °C | Operating temperature       | -10...50 °C |
| Operating temperature, min. | -10 °C      | Operating temperature, max. | 50 °C       |

### General Data

|                    |  |                       |                  |
|--------------------|--|-----------------------|------------------|
| Cable              | Cable LiYCY                              | Cable length          | 0.5 m            |
| Connector PLC side | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) | Interface connector   | SUB-D FEMALE 9P  |
| Material           | PVC                                      | Number of poles, min. | 9-pole           |
| Outer diameter     | 7,8 ± 1 mm                               | Suitable for          | Analogue signals |
| Wire cross-section | 0.25 mm <sup>2</sup>                     |                       |                  |

### Electrical Data

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Capacity wire / shield | 300 pF/m            | Capacity wire / wires                       | 300 pF/m  |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max.    | 3 A                 |   |           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

### Approvals

ROHS Conform

### Downloads

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">Colours chart</a>            |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |