

## VPU II 0 75V/30KA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



### Spare arrester Type II

Weidmüller VPU II surge protection products protect low-voltage consumer installations and electronic devices against overvoltages that can occur as a result of atmospheric discharges (thunderstorms) or switching operations (transients). The VPU II series meets the Type II and Type III requirements acc. to IEC 61643-11:2012 and Type 2 and Type 3 requirements acc. to EN 61643-11:2012. The spare arresters are coded and can only be inserted into suitable bases.

### General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	<a href="#">1350530000</a>
Type	VPU II 0 75V/30KA
GTIN (EAN)	4050118157277
Qty.	1 pc(s).

## VPU II 0 75V/30KA

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	52 mm	Height (inches)	2.047 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	77 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Humidity	5 - 95% rel. humidity		

## General data

Colour	orange	Design	Installation housing; 1TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	UL 94 flammability rating	V-0
Version	Spare arrester		

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

## Rated data IEC / EN

Combined pulse $U_{OC}$	10 kV	Discharge current $I_n$ (8/20 $\mu$ s) wire-PE	15 kA
Energy coordination ( $\leq 10$ m)	Type II, Type III	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	125 A gL > (if back up fuse > 125 A), No Fuse necessary $\leq 125$ A gG
Leakage current at $U_n$	30 $\mu$ A	Max. continuous voltage, $U_c$ (AC)	75 V
Number of poles	1	Protection level $U_p$ at $I_N$ (L/N-PE)	$\leq 0.65$ kV
Rated voltage (AC)	48 V	Requirements category acc. to IEC 61643-11	Type II, Type III
Requirements class, acc. to EN 61643-11	T2, T3	Response time	$\leq 25$ ns
Short-circuit current rating $I_{SCCR}$	25 kA	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	92 V	Voltage type	AC

## Connection data

Type of connection	pluggable
--------------------	-----------

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

**Data sheet**

**VPU II 0 75V/30KA**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

Spare arrester for surge voltage arrester VPU II 75 V series The pluggable high-performance varistors can be swapped by trained personnel following a failure. Rated voltage: 75 V Type: Weidmüller VPU II 0 75 V/40 kA Order no.: 1350530000

**Technical data**

**Tender specification sheets**

Long specification	Spare arrester consisting of V0 material for surge voltage arrester VPU II 75 V series The pluggable high-performance varistors can be exchanged by trained personnel following a failure. Rated voltage: 75 V Type: Weidmüller VPU II 0 75 V/40 kA Order No.: 1350530000	Short specification	<a href="http://www.weidmueller.com">www.weidmueller.com</a>
--------------------	---	---------------------	--

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EAC VPU SERIES</a> <a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**VPU II 0 75V/30KA**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Drawings**

**Electric symbol**

