


TBY-ADV551-CF-PS-2KB-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The digital output interfaces via relay are used to isolate the field sensors from the card and/or to adapt the operation of the said elements to the voltage required by the DCS. The interfaces also support additional characteristics that provide many benefits such as:

- **Redundancy: the interfaces have 2 50-pole (AKB) connectors for redundancy purposes.**
- **Many of the interfaces activate a relay to indicate if one of the two possible power sources has dropped below a value of approximately 12 V**
- **The cards can be mounted via tension clamp or screw connection.**
- **The input sensors can be connected in two ways: supplied with power directly from the card or directly from the field.**

General ordering data

Version	Interface, RS, 2 x AKB (50P), LM2NZF 5.08mm
Order No.	1379510000
Type	TBY-ADV551-CF-PS-2KB-Z
GTIN (EAN)	4050118207163
Qty.	1 pc(s).

TBY-ADV551-CF-PS-2KB-Z
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data
Dimensions and weights

Depth	80 mm	Depth (inches)	3.15 inch
Height	131 mm	Height (inches)	5.157 inch
Width	303 mm	Width (inches)	11.929 inch
Net weight	802.72 g		

Temperatures

Storage temperature	-40...85 °C	Operating temperature	-25...70 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	70 °C

General data

LED status display per relay	green	Disconnecter per relay	No
Fuse per relay	No	Switch	No
LED status of the supply voltage	green	Power supply fuse	1 A

Connection data

Connection (field side)	LM2NZF 5.08mm	Connection on control side	2 x AKB (50P)
Connection supply	LMNZF 5.08mm	Number of poles (control side)	50-pole plug

Rating data

Mechanical service life	5 x 10 ⁶ switching cycles
-------------------------	--------------------------------------

Ratings data input

Input voltage	24 V DC ± 10%	Input current	13 mA
---------------	---------------	---------------	-------

Ratings data output

Relay type	RSS	Contact material	AgNi 90/10
Rated voltage	250 V AC	Max. AC continuous current	2.5 A
Minimum contact current	0.1 A	Minimum contact voltage	5 V

Insulation coordinates (EN50178)

Rated insulation voltage	≤ 50 V DC	Rated input insulation voltage	≤ 50 V DC
Rated output insulation voltage	250 V AC	Overvoltage category input/input	II
Overvoltage category input/output	III	Overvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	≥ 5.5 mm
Clearance input/input	≥ 5.5 mm		

Connection field

Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	1.5 mm ²	Flexible with sleeve, min.	0.25 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 24
Sleeve with plastic collar, max.	1.5 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.2 mm ²	Stripping length	7.5 mm
Type of connection	Tension-clamp connection		

Creation date March 8, 2023 10:24:50 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2

TBY-ADV551-CF-PS-2KB-Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Supply connection**

Type of connection	Tension-clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Ferrule with plastic collar, max.	1.5 mm ²
Wire cross-section, min. AWG	AWG 14	Wire cross-section, max. AWG	AWG 24
Stripping length	7.5 mm		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9dd73319-d286-43a8-a0b7-6458fd2c03f9

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Catalogues	Catalogues in PDF-format
Brochures	

TBY-ADV551-CF-PS-2KB-Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

