

THM WO VIN 17.8/34 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4.4 - 6.7 mm, 17.8 x 34 mm, white
Order No.	1382930000
Type	THM WO VIN 17.8/34 WS
GTIN (EAN)	4050118185065
Qty.	1 Stück
compatible printer	2599430000 2599440000

Erstellungs-Datum May 16, 2023 11:31:05 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

THM WO VIN 17.8/34 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	17.8 mm	Height (inches)	0.701 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	470 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Vinyl film	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	3,000	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Size of labelling field	13 x 17.8 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	34 mm		

Conductor and cable markers

Conductor O.D.	4.4 - 6.7 mm	Conductor O.D., max.	6.7 mm
Conductor O.D., min.	4.4 mm	Conductor cross-section, max.	35 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 35 mm ²
Halogen	Yes	Text field height	13 mm
Text field width	17.8 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

