

## THM WO VIN 12/18 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 2.9 - 2.9 mm, 12 x 18 mm, white
Order No.	<a href="#">1382940000</a>
Type	THM WO VIN 12/18 WS
GTIN (EAN)	4050118185171
Qty.	1 Stück
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

Erstellungs-Datum May 16, 2023 11:31:14 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## THM WO VIN 12/18 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	12 mm	Height (inches)	0.472 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	588 g		

### Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

### General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Vinyl film	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	10,000	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Size of labelling field	9 x 12 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	18 mm		

### Conductor and cable markers

Conductor O.D.	2.9 - 2.9 mm	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.9 mm	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Cross-section for connected wire	0.75 - 6 mm <sup>2</sup>
Halogen	Yes	Text field height	9 mm
Text field width	12 mm		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Zeichnungen**

