

SM 46/46-30 MC NE GR


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	SwitchMark, Device markers, 46 x 46 mm, for cam switches, Type S0, Kraus & Naimer, grey
Order No.	1323520000
Type	SM 46/46-30 MC NE GR
GTIN (EAN)	4050118126839
Qty.	20 Stück
compatible printer	2715590000 2438520000 2438510000

SM 46/46-30 MC NE GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	46 mm	Height (inches)	1.811 inch
Width	46 mm	Width (inches)	1.811 inch
Diameter	30 mm	Net weight	5.2 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Application/manufacturere	for cam switches, Type SO, Kraus & Naimer	Colour	grey
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	8	Number of markers per combination	1 MultiCard = Device markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	UL 94 flammability rating	V-2
Width	46 mm		

Device markers

Diameter	30 mm	Halogen	No
----------	-------	---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

SM 46/46-30 MC NE GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

