

CC-M 30/60 2X3 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | MetalliCard, Device markers, 30 x 60 mm, silver |
| Order No. | 1327850000 |
| Type | CC-M 30/60 2X3 AL |
| GTIN (EAN) | 4050118132700 |
| Qty. | 100 Stück |

CC-M 30/60 2X3 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.5 mm | Depth (inches) | 0.02 inch |
| Height | 30 mm | Height (inches) | 1.181 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Net weight | 2.2 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...130 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--------------------------------|-----------------------------------|--|
| Colour | silver | Material | Chrome coated aluminium (AL), Anodized aluminium |
| Number of markers per combination | 1 MetalliCard = Device markers | Operating temperature range | -55...130 °C |
| Operating temperature range, max. | 130 °C | Operating temperature range, min. | -55 °C |
| Recommended industries | Energy, Process | Size of labelling field | 30.2 x 57.2 mm |
| Width | 60 mm | | |

Device markers

| | |
|---------------------|--------|
| Drill-hole diameter | 3.3 mm |
|---------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

CC-M 30/60 2X3 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Example of use

