

## PAC-UNIV-D15F-F-10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |   |
|------------|---|
| Version    | Pre-assembled cable, PAC, Cable LiYCY, 8.7 ± 1 mm |
| Order No.  | <a href="#">1350480100</a>                        |
| Type       | PAC-UNIV-D15F-F-10M                               |
| GTIN (EAN) | 4032248375660                                     |
| Qty.       | 1 Stück   |

Erstellungs-Datum June 2, 2023 9:12:16 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## PAC-UNIV-D15F-F-10M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 1,031 g

### Temperatures

|                             |             |                             |             |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature         | -10...60 °C | Operating temperature       | -10...50 °C |
| Operating temperature, min. | -10 °C      | Operating temperature, max. | 50 °C       |

### General Data

|                    |  |                       |                  |
|--------------------|--|-----------------------|------------------|
| Cable              | Cable LiYCY                              | Cable length          | 10 m             |
| Connector PLC side | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) | Interface connector   | SUB-D FEMALE 15P |
| Material           | PVC                                      | Number of poles, min. | 15-pole          |
| Outer diameter     | 8.7 ± 1 mm                               | Suitable for          | Analogue signals |
| Wire cross-section | 0.25 mm <sup>2</sup>                     |                       |                  |

### Electrical Data

|   |           |                       |                     |
|---|-----------|-----------------------|---------------------|
| Capacity wire / shield                      | 300 pF/m  | Capacity wire / wires | 300 pF/m            |
| High voltage test                           | 1 KV/1s   | Operating voltage     | ≤ 60 V DC ≤ 25 V AC |
| Permissible current strength per path, max. | 1 A       | Rated voltage         | ≤ 60 Vdc ≤ 25 Vac   |
| Resistance                                  | ≤ 80 mΩ/m | Total current, max.   | 3 A                 |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

### Approvals

ROHS Conform

### Downloads

User Documentation [Colours chart](#)  
 Catalogues [Catalogues in PDF-format](#)