

THM WO 15/70 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 9.6 - 12.7 mm, 15 x 70 mm, white
Order No.	1429440000
Type	THM WO 15/70 WS
GTIN (EAN)	4050118233872
Qty.	1 Stück
compatible printer	2599430000 2599440000

Erstellungs-Datum May 16, 2023 11:42:22 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.591 inch
Width	70 mm	Width (inches)	2.756 inch
Net weight	112 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	500	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	30 x 15 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	70 mm		

Conductor and cable markers

Conductor O.D.	9.6 - 12.7 mm	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	9.6 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 120 mm ²
Halogen	No	Text field height	30 mm
Text field width	15 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

