

TM-I 23 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	TM-I, Insert markers, 23 x 4 mm, To customer specification
Order No.	1433880000
Type	TM-I 23 MC SDR
GTIN (EAN)	4050118238570
Qty.	80 Stück
compatible printer	2715590000 2438520000 2438510000

TM-I 23 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	23 mm	Height (inches)	0.906 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.225 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Insert markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Orientation of print	horizontal
Printed characters	Based on customer requirements (Please send M-Print PRO file)	Printing method	MC Laser
Type of printing	To customer specification	UL 94 flammability rating	V-2
Width	4 mm		

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format