

IE-FM6Z2LO0001MLD0LD0-X**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO

General ordering data

| | |
|------------|---|
| Version | Patch cable, duplex clip included, LC-Duplex IP 20, LC-Duplex IP 20, 62.5 µm, LSZH, 1 m |
| Order No. | 1433930010 |
| Type | IE-FM6Z2LO0001MLD0LD0-X |
| GTIN (EAN) | 4050118242539 |
| Qty. | 1 Stück |

IE-FM6Z2LO0001MLD0LDO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|------|-----------------|------------|
| Length | 1 m | Length (inches) | 39.37 inch |
| Net weight | 21 g | | |

Temperatures

| | | | |
|-----------------------------|----------------|-----------------------------|--------|
| Operating temperature | -20 °C...70 °C | Operating temperature, min. | -20 °C |
| Operating temperature, max. | 70 °C | | |

Cable specific standards

| | | | |
|--|-------------|---|-------------------------------|
| Specification for checking the symmetrical communication cabling | IEC 61935-3 | Specification for twisted-pair device connection cables | IEC 61156-6, DIN EN 50288-4-2 |
|--|-------------|---|-------------------------------|

General standards

| | |
|--------------------|--------------|
| Connector standard | IEC 61754-20 |
|--------------------|--------------|

Standards

| | |
|--------------------|--------------|
| Connector standard | IEC 61754-20 |
|--------------------|--------------|

Cable structure

| | | | |
|-----------------------|--------------|------------------|---------|
| Cable layout | ZIPCORD | Core diameter | 62.5 µm |
| Material sheath | LSZH | Primary coating | 245 µm |
| Sheath diameter | 2.0 * 4.1 mm | Sheathing colour | orange |
| Standard designations | I-V(ZN)H | | |

Mechanical and material properties of cable

| | | | |
|---------------------------------|-------|--------------------------------|-------------|
| Halogen | No | Min. bending radius, once only | 20 mm |
| Min. bending radius, repetitive | 40 mm | Resistance to spread of flame | IEC 60754-2 |

Plug

| | | |
|----------------------------|--|--------------|
| Plug | Cable side | left |
| | Version of contact face | LC-Duplex |
| | Protection degree (IP) | IP20 |
| | Gender of contact | male contact |
| | Outlet direction | straight |
| | Version of connector | plug |
| | Housing main material | Plastic |
| | Status indicator available | No |
| | Shielding available | No |
| | Cable side | right |
| | Version of contact face | LC-Duplex |
| | Protection degree (IP) | IP20 |
| | Gender of contact | male contact |
| | Outlet direction | straight |
| Version of connector | plug | |
| Housing main material | Plastic | |
| Status indicator available | No | |
| Shielding available | No | |
| Plug left | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded | |
| Plug right | LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded | |

Erstellungs-Datum May 22, 2023 2:16:27 PM CEST

IE-FM6Z2LO0001MLD0LDO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technische Daten

info@weidmueller.com

www.weidmueller.com
 LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Plug, left

Connector left
 Plug left
 LC-Duplex IP 20

Plug, right

Connector right
 Plug right
 LC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002607 | ETIM 7.0 | EC002607 |
| ETIM 8.0 | EC002607 | ECLASS 9.0 | 27-06-10-03 |
| ECLASS 9.1 | 27-06-10-03 | ECLASS 10.0 | 27-06-10-03 |
| ECLASS 11.0 | 27-06-10-03 | ECLASS 12.0 | 27-06-10-03 |

Approvals

ROHS Conform

Downloads

| | |
|--------------------|---|
| User Documentation | MAN IE GUIDE DE MAN IE GUIDE EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN |

IE-FM6Z2LO0001MLD0LDO-X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Detailed drawing

