

**WSI 25/3 10X38/LED****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

**General ordering data**

Version	W-Series, Fuse terminal, Rated cross-section: 25 mm <sup>2</sup> , Screw connection
Order No.	<a href="#">1444240000</a>
Type	WSI 25/3 10X38/LED
GTIN (EAN)	4050118249552
Qty.	4 pc(s).

Creation date March 8, 2023 11:07:58 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## WSI 25/3 10X38/LED

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	58 mm	Depth (inches)	2.283 inch
Height	81 mm	Height (inches)	3.189 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	104 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

### Material data

Material	PA 66/6	Colour	dark beige
UL 94 flammability rating	V-0		

### System specifications

Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

### 2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Wire connection cross section, finely stranded, two clampable wires, min.	0.75 mm <sup>2</sup>	Wire cross-section, finely stranded, two clampable wires, max.	10 mm <sup>2</sup>
---	----------------------	--	--------------------

### Additional technical data

Type of mounting	Snap-on
------------------	---------

## WSI 25/3 10X38/LED

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Conductors for clamping (rated connection)

Clampable conductor		Connection specification		Screw connection		
	Cross-section for conductor connection	Type	solid, H05(07) V-U			
		min.	1.5 mm <sup>2</sup>			
		max.	25 mm <sup>2</sup>			
		nominal	25 mm <sup>2</sup>			
	wire end ferrule	Stripping length	min.	11 mm		
			max.	11 mm		
			nominal	11 mm		
		Tightening torque	min.	2 Nm		
			max.	2.5 Nm		
	Recommended wire-end ferrule					
	Connection specification		Screw connection			
	Cross-section for conductor connection	Type	stranded, H07V-R			
min.		1.5 mm <sup>2</sup>				
max.		25 mm <sup>2</sup>				
nominal		25 mm <sup>2</sup>				
wire end ferrule	Stripping length	min.	11 mm			
		max.	11 mm			
		nominal	11 mm			
	Tightening torque	min.	2 Nm			
		max.	2.5 Nm			
Recommended wire-end ferrule						
Connection specification		Screw connection				
Cross-section for conductor connection	Type	flexible, H05(07) V-K				
	min.	1.5 mm <sup>2</sup>				
	max.	25 mm <sup>2</sup>				
	nominal	25 mm <sup>2</sup>				
wire end ferrule	Stripping length	min.	11 mm			
		max.	11 mm			
		nominal	11 mm			
	Tightening torque	min.	2 Nm			
		max.	2.5 Nm			
Recommended wire-end ferrule						
Number of connections	2					
Stripping length	11 mm					
Type of connection	Screw connection					

### Fuse terminals

Cartridge fuse	max. 3W for gG/gL max. 1.2W for aM
----------------	---------------------------------------

### General

Rail	TS 35
------	-------

## WSI 25/3 10X38/LED

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rating data

Rated cross-section	25 mm <sup>2</sup>	Rated voltage	690 V
Rated voltage to adjoining terminal	690 V	Rated current	32 A
Current at maximum wires	32 A	Volume resistance according to IEC 60947-7-x	0.32 mΩ
Rated impulse withstand voltage	6 kV	Power loss in accordance with IEC 60947-7-x	3.23 W
Pollution severity	3		

## Classifications

ETIM 6.0	EC000899	ETIM 7.0	EC000899
ETIM 8.0	EC000899	ECLASS 9.0	27-14-11-16
ECLASS 9.1	27-14-11-16	ECLASS 10.0	27-14-11-16
ECLASS 11.0	27-14-11-16	ECLASS 12.0	27-14-11-16

## Important note

Product information      The voltage depends on the selected fuse element or the selected indicator light

## Approvals

Approvals



ROHS      Conform

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">CE Declaration of Conformity</a> <a href="#">UKCA declaration of conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**WSI 25/3 10X38/LED**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

