

## IE-FCI-D9-FM

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

### General ordering data

Version	FrontCom, Signal insert D-Sub, 9-pole, Plug, Socket connector
Order No.	<a href="#">1450850000</a>
Type	IE-FCI-D9-FM
GTIN (EAN)	4050118255713
Qty.	1 pc(s).

Creation date March 8, 2023 11:36:02 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## IE-FCI-D9-FM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	17.9 mm	Height (inches)	0.705 inch
Width	12.5 mm	Width (inches)	0.492 inch
Length	30.8 mm	Length (inches)	1.213 inch
Net weight	11 g		

## Temperatures

Operating temperature	-55 °C...105 °C	Operating temperature, min.	-55 °C
Operating temperature, max.	105 °C		

## Technical data

Contact resistance	≤ 20 mΩ	Contact surface	Gold-plated
Current-carrying capacity	3 A	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Housing main material	SPCC	Housing surface	tin-plated
Insulation strength	1000 MΩ at 500 V DC	Material insulator	PBT glass fibre reinforced UL 94 V-0
Number of poles	9		

## General data

Insert type	Signal insert D-Sub, 9-pole	Protection degree	IP20
-------------	-----------------------------	-------------------	------

## Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Insulation strength	1000 MΩ at 500 V DC		

## General standards

Certificate No. (UR)	E497345
----------------------	---------

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-18-90-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-18-28-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E497345

Creation date March 8, 2023 11:36:02 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**Data sheet****IE-FCI-D9-FM****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">GL_FrontCom</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB FREECONCONTACT EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

---

**Data sheet**


**IE-FCI-D9-FM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Dimensioned drawing**



**Dimensioned drawing**

