

PAC-S1500-UNIS-V0-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm ²
Order No.	1466240030
Type	PAC-S1500-UNIS-V0-3M
GTIN (EAN)	4032248344673
Qty.	1 Stück

PAC-S1500-UNIS-V0-3M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 782 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
Operating temperature, min.	-10 °C	Operating temperature, max.	50 °C

General Data

Cable	Cable LiYCY	Cable length	3 m
Connector PLC side	SIEMENS S7 1500 6ES7592-1AM00-0XBO 40P	Interface connector	H0.25/10 (FERRULES 0.25mm ²)
Material	PVC	Number of poles, min.	40-pole
Outer diameter	12.4 ± 1 mm	Suitable for	Analogue signals
Wire cross-section	0.25 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Permissible current strength per path, max.	1 A
Rated voltage	≤ 250 Vdc ≤ 250 Vac	Resistance	≤ 80 mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4bbf2c0d-0764-4fc8-bb24-9351c28c190d

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--