

## THM WO 15/140 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 22.3 - 22.3 mm, 15 x 140 mm, white
Order No.	<a href="#">1429450000</a>
Type	THM WO 15/140 WS
GTIN (EAN)	4050118233902
Qty.	1 Stück
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

Erstellungs-Datum May 16, 2023 11:42:31 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## THM WO 15/140 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	15 mm	Height (inches)	0.591 inch
Width	140 mm	Width (inches)	5.512 inch
Net weight	196 g		

### Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

### General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	500	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	70 x 15 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	140 mm		

### Conductor and cable markers

Conductor O.D.	22.3 - 22.3 mm	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	22.3 mm	Conductor cross-section, max.	323 mm <sup>2</sup>
Conductor cross-section, min.	323 mm <sup>2</sup>	Cross-section for connected wire	323 - 323 mm <sup>2</sup>
Halogen	No	Text field height	70 mm
Text field width	15 mm		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**THM WO 15/140 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

