

**H1,5/14 R SP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

- Polypropylene conical cable entry funnel
- Heat-resistant up to 105°C

For conductors from 0.14 – 150 mm<sup>2</sup> (AWG 26-300 MCM)

Material: E-Cu, tin galvanised

Dimensional tolerance acc. to DIN 46228 sect. 4

**General ordering data**

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, red
Order No.	<a href="#">1476270000</a>
Type	H1,5/14 R SP
GTIN (EAN)	4050118283099
Qty.	100 pc(s).

Creation date March 8, 2023 12:35:12 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**H1,5/14 R SP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.026 g

**Technical data**

Description of article	Wire end ferrule with plastic collar, red	Version	Standard

**Wire-end ferrules**

Collar diameter (D2)	3.5 mm	Colour code	Weidmüller
Conductor cross-section	1.5 mm <sup>2</sup>	Contact surface diameter (D1)	1.7 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 16

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

**Downloads**

User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**H1,5/14 R SP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

