

RSM-16 115VAC/DC 1CO Z

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Relay bases (RSM) with common positive and negative to be connected to PLC or other type of controllers. The interfaces are made up of groups of 4, 8 or 16 RCL relays (12.7 mm) or RSS (6.1 mm). The connection to the controller can be set up using pluggable connectors or using direct cabling with IEC 60603-13 connectors. Wide range of options:

- 1 or 2 CO contacts with 16/8/6 A relays
- Voltages from 5 to 230 V
- Screw, tension clamp or PUSH IN connection
- Compatible with Weidmüller's solid-state relays

The range of relays provides galvanic isolation between input/output as well as between the adjacent contacts on the relays. This enables the various voltages in the controllers and those required by the various field elements to be safely adapted.

General ordering data

Version	Interface, RSM, PUSH IN
Order No.	1448400000
Type	RSM-16 115VAC/DC 1CO Z
GTIN (EAN)	4050118252828
Qty.	1 pc(s).

RSM-16 115VAC/DC 1CO Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	66 mm	Depth (inches)	2.598 inch
Height	87 mm	Height (inches)	3.425 inch
Width	259 mm	Width (inches)	10.197 inch
Net weight	504.85 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	50 °C

General data

LED status display per relay	green
------------------------------	-------

Connection data

Connection (field side)	LMFS 5.08 mm	Connection on control side	LMFS 5.08 mm
-------------------------	--------------	----------------------------	--------------

Rating data

Mechanical service life	30 x 10 ⁶ switching cycles
-------------------------	---------------------------------------

Ratings data input

Input voltage	115 VAC/DC ± 10%	Input current	AC 3.3 mA / DC 4.8 mA
---------------	------------------	---------------	-----------------------

Ratings data output

Relay type	RCL	Type of output	Potential-free contact
Contact material	AgNi 90/10	Rated voltage	≤ 250 V AC
Max. AC continuous current	6 A	Minimum contact current	0.1 A
Minimum contact voltage	5 V		

Insulation coordination (EN50178)

Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC		

Insulation coordinates (EN50178)

Rated input insulation voltage	< 50 V AC	Rated output insulation voltage	250 V AC
Oversvoltage category input/output	III	Oversvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	≥ 5.5 mm

Connection field

Clamping range, max.	2.5 mm ²	Clamping range, min.	0.12 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible, max. H05(07) V-K	2.5 mm ²
Flexible, min. H05(07) V-K	0.02 mm ²	Max. wire cross-section, AWG	AWG 12
Min. wire cross-section, AWG	AWG 26	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.12 mm ²	Stripping length	10 mm
Type of connection	PUSH IN		

Creation date March 8, 2023 11:19:35 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2

RSM-16 115VAC/DC 1CO Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

RSM-16 115VAC/DC 1CO Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

