

**HSS 3.2-9.5 EL W13M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 3.2 - 9.5 mm, white
Order No.	<a href="#">1489660000</a>
Type	HSS 3.2-9.5 EL W13M
GTIN (EAN)	4050118299359
Qty.	1 Stück
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

Erstellungs-Datum May 16, 2023 12:19:03 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## HSS 3.2-9.5 EL W13M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.03 inch
Width	15.1 mm	Width (inches)	0.594 inch
Length	13,000 mm	Length (inches)	511.81 inch
Net weight	177 g		

### Temperatures

Operating temperature range	-55...135 °C
-----------------------------	--------------

### General data

Colour	white	Halogen	Yes
Length	13,000 mm	Material	Polyolefine
Operating temperature range	-55...135 °C	Operating temperature range, max.	135 °C
Operating temperature range, min.	-55 °C	Printed characters	without
Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery	Type of printing	neutral
Width	15.1 mm		

### Conductor and cable markers

Conductor O.D.	3.2 - 9.5 mm	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	3.2 mm	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Cross-section for connected wire	4 - 16 mm <sup>2</sup>
Halogen	Yes	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C	Text field height	14.9 mm
Text field width	0 mm		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E366310

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**HSS 3.2-9.5 EL W13M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

