

RSM-4 230VAC 2CO Z

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Relay bases (RSM) with common positive and negative to be connected to PLC or other type of controllers. The interfaces are made up of groups of 4, 8 or 16 RCL relays (12.7 mm) or RSS (6.1 mm). The connection to the controller can be set up using pluggable connectors or using direct cabling with IEC 60603-13 connectors. Wide range of options:

- 1 or 2 CO contacts with 16/8/6 A relays
- Voltages from 5 to 230 V
- Screw, tension clamp or PUSH IN connection
- Compatible with Weidmüller's solid-state relays

The range of relays provides galvanic isolation between input/output as well as between the adjacent contacts on the relays. This enables the various voltages in the controllers and those required by the various field elements to be safely adapted.

General ordering data

| | |
|------------|------------------------------------------|
| Version | Interface, RSM, Tension-clamp connection |
| Order No. | 1448810000 |
| Type | RSM-4 230VAC 2CO Z |
| GTIN (EAN) | 4050118253153 |
| Qty. | 1 pc(s). |

RSM-4 230VAC 2CO Z

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-----------|-----------------|------------|
| Depth | 66 mm | Depth (inches) | 2.598 inch |
| Height | 109 mm | Height (inches) | 4.291 inch |
| Width | 75 mm | Width (inches) | 2.953 inch |
| Net weight | 202.314 g | | |

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
| Operating temperature, min. | -25 °C | Operating temperature, max. | 50 °C |

General data

| | |
|------------------------------|-------|
| LED status display per relay | green |
|------------------------------|-------|

Connection data

| | | | |
|-------------------------|---------------|----------------------------|------|
| Connection (field side) | LM2NZF 5.08mm | Connection on control side | LMZF |
|-------------------------|---------------|----------------------------|------|

Rating data

| | |
|-------------------------|---------------------------------------|
| Mechanical service life | 10 x 10 ⁶ switching cycles |
|-------------------------|---------------------------------------|

Ratings data input

| | | | |
|---------------|----------------|---------------|--------|
| Input voltage | 230 V AC ± 10% | Input current | 3.3 mA |
|---------------|----------------|---------------|--------|

Ratings data output

| | | | |
|----------------------------|------------|-------------------------|------------------------|
| Relay type | RCL | Type of output | Potential-free contact |
| Contact material | AgNi 90/10 | Rated voltage | ≤ 250 V AC |
| Max. AC continuous current | 5 A | Minimum contact current | 0.1 A |
| Minimum contact voltage | 5 V | | |

Insulation coordination (EN50178)

| | | | |
|--------------------------|----------|-------------------------------|------|
| Pollution severity level | 2 | Pulse voltage test (1,2/50µs) | 6 kV |
| Insulation test voltage | 1.2 kVAC | | |

Insulation coordinates (EN50178)

| | | | |
|------------------------------------|-----------|-------------------------------------|----------|
| Rated input insulation voltage | < 50 V AC | Rated output insulation voltage | 250 V AC |
| Oversvoltage category input/output | III | Oversvoltage category output/output | III |
| Pollution severity level | 2 | Pulse voltage test (1,2/50µs) | 6 kV |
| Insulation test voltage | 1.2 kVAC | Clearance input/output | ≥ 5.5 mm |

Connection field

| | | | |
|------------------------------|--------------------------|------------------------------|----------------------|
| Clamping range, max. | 2.5 mm ² | Clamping range, min. | 0.13 mm ² |
| Flexible with sleeve, max. | 1.5 mm ² | Flexible, max. H05(07) V-K | 1.5 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Max. wire cross-section, AWG | AWG 14 |
| Min. wire cross-section, AWG | AWG 26 | Solid, max. H05(07) V-U | 1.5 mm ² |
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 7 mm |
| Type of connection | Tension-clamp connection | | |

Creation date March 8, 2023 11:23:48 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

RSM-4 230VAC 2CO Z**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Classifications**

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002780 | ETIM 7.0 | EC002780 |
| ETIM 8.0 | EC002780 | ECLASS 9.0 | 27-14-11-52 |
| ECLASS 9.1 | 27-24-22-16 | ECLASS 10.0 | 27-14-11-52 |
| ECLASS 11.0 | 27-14-11-52 | ECLASS 12.0 | 27-14-11-52 |

Environmental Product Compliance

| | |
|------------|----------------------------------------------------|
| REACH SVHC | Lead 7439-92-1 4,4'-isopropylidenediphenol 80-05-7 |
| SCIP | 66e752f3-a24f-4fef-89c4-f29f52d01390 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---------------------------------------------|-------------------------------------------|
| Approval/Certificate/Document of Conformity | Declaration of Conformity |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

RSM-4 230VAC 2CO Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

