

**HSS 2.1-6.4 EL W30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | Conductor and cable markers, 2.1 - 6.4 mm, white      |
| Order No.          | <a href="#">1505870000</a>                            |
| Type               | HSS 2.1-6.4 EL W30M                                   |
| GTIN (EAN)         | 4050118314335   |
| Qty.               | 1 Stück   |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

Erstellungs-Datum May 16, 2023 1:10:12 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## HSS 2.1-6.4 EL W30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Depth      | 0.77 mm   | Depth (inches)  | 0.03 inch    |
| Width      | 10.7 mm   | Width (inches)  | 0.421 inch   |
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 210 g     |                 |              |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

### General data

|                                   |   |                                   |             |
|-----------------------------------|---|-----------------------------------|-------------|
| Colour                            | white   | Halogen                           | Yes         |
| Length                            | 30,000 mm   | Material                          | Polyolefine |
| Operating temperature range       | -55...135 °C  | Operating temperature range, max. | 135 °C      |
| Operating temperature range, min. | -55 °C  | Printed characters                | without     |
| Recommended industries            | Plant manufacture, Energy, Device manufacturer, Machinery | Type of printing                  | neutral     |
| Width                             | 10.7 mm   |                                   |             |

### Conductor and cable markers

|                                   |                     |                                  |                         |
|-----------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D.                    | 2.1 - 6.4 mm        | Conductor O.D., max.             | 6.4 mm                  |
| Conductor O.D., min.              | 2.1 mm              | Conductor cross-section, max.    | 6 mm <sup>2</sup>       |
| Conductor cross-section, min.     | 1.5 mm <sup>2</sup> | Cross-section for connected wire | 1.5 - 6 mm <sup>2</sup> |
| Halogen                           | Yes                 | Rate of shrinkage                | 3:1                     |
| Recommended shrinking temperature | 90 °C               | Text field height                | 10.5 mm                 |
| Text field width                  | 0 mm                |                                  |                         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Important note

|                     |   |
|---------------------|---|
| Product information | External roll holder 1302920000 necessary |
|---------------------|---|

### Approvals

|                         |   |
|-------------------------|---|
| Approvals               |  |
| ROHS                    | Conform   |
| UL File Number Search   | UL Website  |
| Certificate No. (cURus) | E366310   |

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

Erstellungs-Datum May 16, 2023 1:10:12 PM CEST

**Datenblatt**

**HSS 2.1-6.4 EL W30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

