

**IE-FSMD2UE0040MSDESDEX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO breakout cable

**General ordering data**

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 9 µm, PUR, 40 m
Order No.	<a href="#">1449420400</a>
Type	IE-FSMD2UE0040MSDESDEX
GTIN (EAN)	4050118258530
Qty.	1 Stück

## IE-FSMD2UE0040MSDESDEX

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	40 m	Length (inches)	1,574,803 inch
Net weight	1,268.08 g		

### Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	-20 °C...60 °C		

### General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

### Standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24
--------------------	--

### Cable structure

Cable layout	Break-out dragline	Core diameter	9 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

### Mechanical and material properties of cable

Bending cycles	100,000	Halogen	No
Min. bending radius, once only	25 mm	Min. bending radius, repetitive	77 mm

### Plug

Plug	Cable side	left
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	No
	Cable side	right
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	PushPull V14
Version of connector	plug	
Housing main material	Zinc diecast	
Status indicator available	No	
Shielding available	No	
Plug left	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded	
Plug right	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded	

Erstellungs-Datum May 22, 2023 2:23:13 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

**IE-FSMD2UE0040MSDESDEX**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com) SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded

**Technische Daten**

**Plug, left**

Connector left	Plug left	SC IP 67 PushPull V14 metal	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
----------------	-----------	-----------------------------	--

**Plug, right**

Connector right	Plug right	SC IP 67 PushPull V14 metal	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
-----------------	------------	-----------------------------	--

**Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-FSMD2UE0040MSDESDEX**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Detailed drawing**

