

**IE-C6KS8VG0030XCSXXX-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables, PROFINET, Cat 6<sub>A</sub>, PVC, green,  
M12 X-type

**General ordering data**

Version	Connecting line, M12 X-type IP 67 straight male, Open, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010), PVC, 3 m
Order No.	<a href="#">1449470030</a>
Type	IE-C6KS8VG0030XCSXXX-E
GTIN (EAN)	4050118264173
Qty.	1 pc(s).

Creation date March 13, 2023 2:09:11 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**IE-C6KS8VG0030XCSXXX-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	3 m	Length (inches)	118.11 inch
Net weight	0.001 g		

**Temperatures**

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	-40 °C...80 °C		

**Cable specific standards**

Standard, assembly	UL-Style 2461
--------------------	---------------

**Standards**

Standard, assembly	UL-Style 2461
--------------------	---------------

**Cable structure**

Colour sequence or wires - wire pairs	white/blue - blue, white/ orange - orange, white/ green - green, white/ brown - brown	Cross-section	4*2*AWG 23/7
Insulation cross-section	1.58 mm	Material sheath	PVC
Sheath diameter, max.	8.8 mm	Sheathing colour	green (RAL 6018)
Shielding	S/FTP		

**Electrical properties of cable**

Category	Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)	Speed	10 GBit/s
Test voltage: wire-wire-shield	800 V <sub>eff</sub> , 50 Hz, 1 min		

**Mechanical and material properties of cable**

Halogen	Yes	Min. bending radius, once only	4 x cable diameter
Min. bending radius, repetitive	8 x cable diameter	Pulling force	≤ 150 N
Resistance to spread of flame	in accordance with IEC 60332-1-2	Speed	10 GBit/s

**Plug**

Plug left	M12, X, IP67, male contact, straight, plug, Plastic, shielded	Plug right	free conductor end
-----------	---	------------	--------------------

**Plug, left**

Connector left	M12 X-type IP 67 straight male
----------------	-----------------------------------

**Plug, right**

Connector right	Open
-----------------	------

Creation date March 13, 2023 2:09:11 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2

**IE-C6KS8VG0030XCSXXX-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">PROFINET Manufacturer's Declaration</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**Data sheet**

**IE-C6KS8VG0030XCSXXX-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

---

White, Orange	1	M12
Orange	2	
White, Green	3	
Green	4	
White, Brown	5	
Brown	6	
White, Blue	7	
Blue	8	

---

---

---

---