

## RSMS-16 12V- 1CO Z

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Relay bases (RSM) with common positive and negative to be connected to PLC or other type of controllers. The interfaces are made up of groups of 4, 8 or 16 RCL relays (12.7 mm) or RSS (6.1 mm). The connection to the controller can be set up using pluggable connectors or using direct cabling with IEC 60603-13 connectors. Wide range of options:

- 1 or 2 CO contacts with 16/8/6 A relays
- Voltages from 5 to 230 V
- Screw, tension clamp or PUSH IN connection
- Compatible with Weidmüller's solid-state relays

The range of relays provides galvanic isolation between input/output as well as between the adjacent contacts on the relays. This enables the various voltages in the controllers and those required by the various field elements to be safely adapted.

### General ordering data

Version	Interface, RSM, Tension-clamp connection
Order No.	<a href="#">1457090000</a>
Type	RSMS-16 12V- 1CO Z
GTIN (EAN)	4050118263459
Qty.	1 pc(s).

## RSMS-16 12V- 1CO Z

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	76 mm	Depth (inches)	2.992 inch
Height	109 mm	Height (inches)	4.291 inch
Width	112 mm	Width (inches)	4.409 inch
Net weight	303 g		

### Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	50 °C

### General data

LED status display per relay	green	LED status of the supply voltage	yellow
------------------------------	-------	----------------------------------	--------

### Connection data

Connection (field side)	LM3RZF 5.08	Connection on control side	LMZF
-------------------------	-------------	----------------------------	------

### Rating data

Mechanical service life	5 x 10 <sup>6</sup> switching cycles
-------------------------	--------------------------------------

### Ratings data input

Input voltage	12 V DC ± 10%	Input current	14.2 mA
---------------	---------------	---------------	---------

### Ratings data output

Relay type	RSS	Type of output	Potential-free contact
Contact material	AgNi 90/10	Rated voltage	≤ 250 V AC
Max. AC continuous current	4.5 A	Minimum contact current	100 mA
Minimum contact voltage	5 V		

### Insulation coordination (EN50178)

Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC		

### Insulation coordinates (EN50178)

Rated input insulation voltage	< 50 V AC	Rated output insulation voltage	250 V AC
Overtoltage category input/output	III	Overtoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage	1.2 kVAC	Clearance input/output	≥ 5.5 mm

### Connection field

Clamping range, max.	2.5 mm <sup>2</sup>	Clamping range, min.	0.13 mm <sup>2</sup>
Flexible with sleeve, max.	1.5 mm <sup>2</sup>	Flexible, max. H05(07) V-K	1.5 mm <sup>2</sup>
Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>	Max. wire cross-section, AWG	AWG 14
Min. wire cross-section, AWG	AWG 26	Solid, max. H05(07) V-U	1.5 mm <sup>2</sup>
Solid, min. H05(07) V-U	0.5 mm <sup>2</sup>	Stripping length	7 mm
Type of connection	Tension-clamp connection		

Creation date March 8, 2023 11:45:41 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**Data sheet**

**RSMS-16 12V- 1CO Z**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Classifications**

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	71d9bdc4-a0b5-4af0-93bd-2ad4e523fb14

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**RSMS-16 12V- 1CO Z**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

