

IE-CSQS9VE0050AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	System cable, V14 hybrid (shielded), V14 hybrid (shielded), PVC, 5 m, , Hybrid
Order No.	1465850050
Type	IE-CSQS9VE0050AQEAQE-K1
GTIN (EAN)	4050118272529
Qty.	1 Stück

Erstellungs-Datum May 24, 2023 3:45:07 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-CSQS9VE0050AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	726 g		

Temperatures

Operating temperature	-40 °C...80 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	80 °C		

Electrical properties

Insulation strength	> 500 MΩ	Operating voltage	300 V
---------------------	----------	-------------------	-------

General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	----------------------------------------------

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	----------------------------------------------

Cable structure

Cable layout	Hybrid cable, for permanent installation	Cross-section	2 x 0.34 mm ² + 7 x 0.5 mm ²
Insulation	PP	Insulation cross-section	1.25
Insulation diameter 2	2.15 mm	Material sheath	PVC
Overlap of shielding braid	85 %	Sheath diameter, max.	9.5 mm
Sheath diameter, min.	9.1 mm	Sheathing colour	black

Electrical properties of cable

Insulation strength	> 500 MΩ	Operating voltage	300 V
---------------------	----------	-------------------	-------

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
--------------------------------	--------------------	---------------------------------	---------------------

IE-CSQS9VE0050AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Plug

Plug	Cable side	left
	Version of contact face	Q10 Hybrid
	Protection degree (IP)	IP67
	Gender of contact	female contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	Yes
	Cable side	right
	Version of contact face	Q10 Hybrid
	Protection degree (IP)	IP67
	Gender of contact	female contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	Yes
Plug left	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded	
Plug right	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded	

Plug, left

Connector left	Plug left	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
V14 hybrid (shielded)		

Plug, right

Connector right	Plug right	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
V14 hybrid (shielded)		

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Erstellungs-Datum May 24, 2023 3:45:07 PM CEST

IE-CSQS9VE0050AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN


IE-CSQS9VE0050AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Wiring



STECKANLEITUNG
TYPE 9000

PAAR	BEZEICHNUNG
1	PAAR 1 (S)
2	PAAR 2 (S)
3	PAAR 3 (S)
4	PAAR 4 (S)
5	PAAR 5 (S)
6	PAAR 6 (S)
7	PAAR 7 (S)
8	PAAR 8 (S)
9	PAAR 9 (S)
10	PAAR 10 (S)
11	PAAR 11 (S)
12	PAAR 12 (S)
13	PAAR 13 (S)
14	PAAR 14 (S)
15	PAAR 15 (S)
16	PAAR 16 (S)
17	PAAR 17 (S)
18	PAAR 18 (S)
19	PAAR 19 (S)
20	PAAR 20 (S)
21	PAAR 21 (S)
22	PAAR 22 (S)
23	PAAR 23 (S)
24	PAAR 24 (S)
25	PAAR 25 (S)
26	PAAR 26 (S)
27	PAAR 27 (S)
28	PAAR 28 (S)
29	PAAR 29 (S)
30	PAAR 30 (S)
31	PAAR 31 (S)
32	PAAR 32 (S)
33	PAAR 33 (S)
34	PAAR 34 (S)
35	PAAR 35 (S)
36	PAAR 36 (S)
37	PAAR 37 (S)
38	PAAR 38 (S)
39	PAAR 39 (S)
40	PAAR 40 (S)
41	PAAR 41 (S)
42	PAAR 42 (S)
43	PAAR 43 (S)
44	PAAR 44 (S)
45	PAAR 45 (S)
46	PAAR 46 (S)
47	PAAR 47 (S)
48	PAAR 48 (S)
49	PAAR 49 (S)
50	PAAR 50 (S)