

IE-CSQS9VE0080AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	System cable, V14 hybrid (shielded), V14 hybrid (shielded), PVC, 8 m, , Hybrid
Order No.	1465850080
Type	IE-CSQS9VE0080AQEAQE-K1
GTIN (EAN)	4050118272420
Qty.	1 Stück

Erstellungs-Datum May 24, 2023 3:45:16 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-CSQS9VE0080AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	8 m	Length (inches)	314.961 inch
Net weight	1,096 g		

Temperatures

Operating temperature	-40 °C...80 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	80 °C		

Electrical properties

Insulation strength	> 500 MΩ	Operating voltage	300 V
---------------------	----------	-------------------	-------

General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Cable structure

Cable layout	Hybrid cable, for permanent installation	Cross-section	2 x 0.34 mm ² + 7 x 0.5 mm ²
Insulation	PP	Insulation cross-section	1.25
Insulation diameter 2	2.15 mm	Material sheath	PVC
Overlap of shielding braid	85 %	Sheath diameter, max.	9.5 mm
Sheath diameter, min.	9.1 mm	Sheathing colour	black

Electrical properties of cable

Insulation strength	> 500 MΩ	Operating voltage	300 V
---------------------	----------	-------------------	-------

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
--------------------------------	--------------------	---------------------------------	---------------------

IE-CSQS9VE0080AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Plug

Plug	Cable side	left
	Version of contact face	Q10 Hybrid
	Protection degree (IP)	IP67
	Gender of contact	female contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	Yes
	Cable side	right
	Version of contact face	Q10 Hybrid
	Protection degree (IP)	IP67
	Gender of contact	female contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	Yes
Plug left	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded	
Plug right	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded	

Plug, left

Connector left	Plug left	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
V14 hybrid (shielded)		

Plug, right

Connector right	Plug right	Q10 Hybrid, IP67, female contact, straight, PushPull V14, plug, Zinc diecast, shielded
V14 hybrid (shielded)		

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Erstellungs-Datum May 24, 2023 3:45:16 PM CEST

IE-CSQS9VE0080AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN


IE-CSQS9VE0080AQEAQE-K1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Wiring



STECKANLEITUNG
TYPE 9080

PAAR	BEZEICHNUNG
1	PAAR 1 (S)
2	PAAR 2 (S)
3	PAAR 3 (S)
4	PAAR 4 (S)
5	PAAR 5 (S)
6	PAAR 6 (S)
7	PAAR 7 (S)
8	PAAR 8 (S)
9	PAAR 9 (S)
10	PAAR 10 (S)
11	PAAR 11 (S)
12	PAAR 12 (S)
13	PAAR 13 (S)
14	PAAR 14 (S)
15	PAAR 15 (S)
16	PAAR 16 (S)
17	PAAR 17 (S)
18	PAAR 18 (S)
19	PAAR 19 (S)
20	PAAR 20 (S)
21	PAAR 21 (S)
22	PAAR 22 (S)
23	PAAR 23 (S)
24	PAAR 24 (S)
25	PAAR 25 (S)
26	PAAR 26 (S)
27	PAAR 27 (S)
28	PAAR 28 (S)
29	PAAR 29 (S)
30	PAAR 30 (S)
31	PAAR 31 (S)
32	PAAR 32 (S)
33	PAAR 33 (S)
34	PAAR 34 (S)
35	PAAR 35 (S)
36	PAAR 36 (S)
37	PAAR 37 (S)
38	PAAR 38 (S)
39	PAAR 39 (S)
40	PAAR 40 (S)
41	PAAR 41 (S)
42	PAAR 42 (S)
43	PAAR 43 (S)
44	PAAR 44 (S)
45	PAAR 45 (S)
46	PAAR 46 (S)
47	PAAR 47 (S)
48	PAAR 48 (S)
49	PAAR 49 (S)
50	PAAR 50 (S)
51	PAAR 51 (S)
52	PAAR 52 (S)
53	PAAR 53 (S)
54	PAAR 54 (S)
55	PAAR 55 (S)
56	PAAR 56 (S)
57	PAAR 57 (S)
58	PAAR 58 (S)
59	PAAR 59 (S)
60	PAAR 60 (S)
61	PAAR 61 (S)
62	PAAR 62 (S)
63	PAAR 63 (S)
64	PAAR 64 (S)
65	PAAR 65 (S)
66	PAAR 66 (S)
67	PAAR 67 (S)
68	PAAR 68 (S)
69	PAAR 69 (S)
70	PAAR 70 (S)
71	PAAR 71 (S)
72	PAAR 72 (S)
73	PAAR 73 (S)
74	PAAR 74 (S)
75	PAAR 75 (S)
76	PAAR 76 (S)
77	PAAR 77 (S)
78	PAAR 78 (S)
79	PAAR 79 (S)
80	PAAR 80 (S)
81	PAAR 81 (S)
82	PAAR 82 (S)
83	PAAR 83 (S)
84	PAAR 84 (S)
85	PAAR 85 (S)
86	PAAR 86 (S)
87	PAAR 87 (S)
88	PAAR 88 (S)
89	PAAR 89 (S)
90	PAAR 90 (S)
91	PAAR 91 (S)
92	PAAR 92 (S)
93	PAAR 93 (S)
94	PAAR 94 (S)
95	PAAR 95 (S)
96	PAAR 96 (S)
97	PAAR 97 (S)
98	PAAR 98 (S)
99	PAAR 99 (S)
100	PAAR 100 (S)