

## CLI C 2-4 GE/SW M CD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |   |
|------------|---|
| Version    | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No.  | <a href="#">1568261661</a>  |
| Type       | CLI C 2-4 GE/SW M CD  |
| GTIN (EAN) | 4008 190006174  |
| Qty.       | 250 Stück   |

Erstellungs-Datum May 16, 2023 2:44:03 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI C 2-4 GE/SW M CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 8 mm    | Depth (inches)  | 0.315 inch |
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 7 mm    | Width (inches)  | 0.276 inch |
| Net weight | 0.211 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|                                   |                                      |  |                    |
|-----------------------------------|--------------------------------------|--|--------------------|
| Colour                            | yellow                               | Colour of printing                           | black              |
| Halogen                           | Yes                                  | Insulation cross-section, max.               | 10                 |
| Material                          | PVC, soft, without Cadmium           | Material colour according to resistance code | 4                  |
| Number of markers per combination | 1 Reel = Conductor and cable markers | Operating temperature range                  | -30...80 °C        |
| Operating temperature range, max. | 80 °C                                | Operating temperature range, min.            | -30 °C             |
| Orientation of print              | horizontal                           | Printed characters                           | Upper-case letters |
| Printing                          | M                                    | Printing method                              | hot-embossing      |
| Recommended industries            | Process, Machinery                   | Type of printing                             | Standard           |
| UL 94 flammability rating         | V-0                                  | Version                                      | CD                 |
| Width                             | 7 mm                                 |  |                    |

### Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 4 - 10 mm           | Conductor O.D., max.             | 10 mm                    |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max.    | 16 mm <sup>2</sup>       |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">WSCAD, EPLAN</a>   |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**CLI C 2-4 GE/SW M CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration