

CLI M 2-4 GE/SW V CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, yellow |
| Order No. | 1568301681 |
| Type | CLI M 2-4 GE/SW V CD |
| GTIN (EAN) | 4008 190124489 |
| Qty. | 500 Stück |

Erstellungs-Datum May 16, 2023 3:55:23 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CLI M 2-4 GE/SW V CD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 3 mm | Depth (inches) | 0.118 inch |
| Height | 4 mm | Height (inches) | 0.157 inch |
| Width | 11.3 mm | Width (inches) | 0.445 inch |
| Net weight | 0.146 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|--|--------------------|-----------------------------------|--------------------------------------|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4 | Number of markers per combination | 1 Reel = Conductor and cable markers |
| Operating temperature range | -30...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Orientation of print | horizontal |
| Printed characters | Upper-case letters | Printing | V |
| Printing method | hot-embossing | Recommended industries | Process, Machinery |
| Type of printing | Standard | UL 94 flammability rating | V-0 |
| Version | CD | Width | 11.3 mm |

Conductor and cable markers

| | | | |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D. | 10 - 317 mm | Conductor O.D., max. | 317 mm |
| Conductor O.D., min. | 10 mm | Conductor cross-section, max. | 500 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 500 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

CLI M 2-4 GE/SW V CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen



Similar to illustration