

CAN SUB-D SK35 TERM PS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

General ordering data

Version	SUB-D
Order No.	1550610000
Type	CAN SUB-D SK35 TERM PS
GTIN (EAN)	4050118357066
Qty.	1 Stück

CAN SUB-D SK35 TERM PS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	16.8 mm	Depth (inches)	0.661 inch
Height	68.8 mm	Height (inches)	2.709 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	100 g		

Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

Technical specifications for sub-D connector

BUS PG interface	D-Sub 9-pole, Pin	BUS interface	D-Sub 9-pole, Socket
BUS, cable interface	Screw connection	Data rate	1 Mbps
Housing main material	ZnAl	Humidity	Max. 75% at +25°C, non-condensing
Interlock	UNC4-40	Outgoing elbow	35°
Plugging cycles	≥ 200	Programming interface	Yes
Protection degree	IP30	Temperature range of housing	-20...+70 ° C
Terminating resistor available	Yes		

Classifications

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ECLASS 9.0	27-44-03-02
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-02
ECLASS 11.0	27-44-03-02	ECLASS 12.0	27-44-03-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcaaf625

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN