

**HSS-HF 4.8-9.5 EL R30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | Conductor and cable markers, 4.8 - 9.5 mm, red        |
| Order No.          | <a href="#">1562790000</a>                            |
| Type               | HSS-HF 4.8-9.5 EL R30M                                |
| GTIN (EAN)         | 4050118367584   |
| Qty.               | 1 Stück   |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

Erstellungs-Datum May 16, 2023 1:17:25 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## HSS-HF 4.8-9.5 EL R30M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Depth      | 1.2 mm    | Depth (inches)  | 0.047 inch   |
| Width      | 15.1 mm   | Width (inches)  | 0.594 inch   |
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 558 g     |                 |              |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

### General data

|                                   |           |                                   |              |
|-----------------------------------|-----------|-----------------------------------|--------------|
| Colour                            | red       | Halogen                           | No           |
| Length                            | 30,000 mm | Material                          | Polyolefine  |
| Number per roll                   | 1         | Operating temperature range       | -55...105 °C |
| Operating temperature range, max. | 105 °C    | Operating temperature range, min. | -55 °C       |
| Printed characters                | without   | Type of printing                  | neutral      |
| Width                             | 15.1 mm   |                                   |              |

### Conductor and cable markers

|                                   |                   |                                  |                        |
|-----------------------------------|-------------------|----------------------------------|------------------------|
| Conductor O.D.                    | 4.8 - 9.5 mm      | Conductor O.D., max.             | 9.5 mm                 |
| Conductor O.D., min.              | 4.8 mm            | Conductor cross-section, max.    | 16 mm <sup>2</sup>     |
| Conductor cross-section, min.     | 4 mm <sup>2</sup> | Cross-section for connected wire | 4 - 16 mm <sup>2</sup> |
| Halogen                           | No                | Rate of shrinkage                | 2:1                    |
| Recommended shrinking temperature | 90 °C             |                                  |                        |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Important note

|                     |   |
|---------------------|---|
| Product information | External roll holder 1302920000 necessary |
|---------------------|---|

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN ISO 4589-2 1999</a><br><a href="#">EN 45545-2:2020</a> |
| Engineering Data                            | <a href="#">WSCAD, EPLAN</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |

**HSS-HF 4.8-9.5 EL R30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

