

## HDC 10B KBU 1PG16G

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Version	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Coupling housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16
Order No.	<a href="#">1654580000</a>
Type	HDC 10B KBU 1PG16G
GTIN (EAN)	4008190407407
Qty.	1 pc(s).

## HDC 10B KBU 1PG16G

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	115.7 mm	Depth (inches)	4.555 inch
Height	55 mm	Height (inches)	2.165 inch
Width	55 mm	Width (inches)	2.165 inch
Net weight	208 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## Dimensions

Cable entry	w. thread	Height of housing B	54.65 mm
Total length housing	73 mm	Width housing C	43 mm

## General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating		

## Version

BG	4	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 7035
Design	Standard	Design of housing	Coupling housing
Design of locking system	Side-locking clamp on lower side	Internal thread	PG 16
Number of cable entry on top	1	Number of cable entry sideways	0
Sealing	NBR	Size	4
Size of cable entries	PG 16	Suitable for ModuPlug®	No
Top part/bottom part/lid	lower part	Type	coupling extension

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant

Creation date March 6, 2023 8:22:22 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

2

**HDC 10B KBU 1PG16G**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

**Technical data**

info@weidmueller.com

www.weidmueller.com

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-Odda3647412f
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@679dd24e de.myview.objectmodel.impl.BlockImpl@471e8fe7 de.myview.objectmodel.impl.BlockImpl@2644d99a de.myview.objectmodel.impl.BlockImpl@2bc4b9f1 de.myview.objectmodel.impl.BlockImpl@22421165 de.myview.objectmodel.impl.BlockImpl@1110d37d de.myview.objectmodel.impl.BlockImpl@119840cc de.myview.objectmodel.impl.BlockImpl@1f9d683f de.myview.objectmodel.impl.BlockImpl@2de68b90 de.myview.objectmodel.impl.BlockImpl@3a7a3e6a de.myview.objectmodel.impl.BlockImpl@69b787c9 de.myview.objectmodel.impl.BlockImpl@1d1fc650 de.myview.objectmodel.impl.BlockImpl@4bc7468

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20220214 Technical change to HDC housings</a> <a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date March 6, 2023 8:22:22 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.