

## HDC 32B TOBU 1PG29G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Version	HDC enclosures, Size: 10, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 29
Order No.	<a href="#">1666870000</a>
Type	HDC 32B TOBU 1PG29G
GTIN (EAN)	4008190424077
Qty.	1 pc(s).

## HDC 32B TOBU 1PG29G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	94 mm	Depth (inches)	3.701 inch
Height	79 mm	Height (inches)	3.11 inch
Width	98 mm	Width (inches)	3.858 inch
Net weight	384 g		

### Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

### Dimensions

Cable entry	w. thread	Height of housing B	79 mm
Total length housing	94 mm	Width housing C	82.5 mm

### General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	Tightening torque	2 Nm

### Version

BG	10	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 7035
Design	Standard	Design of housing	Cable entry from top, Plug housing
Design of locking system	Side-locking clamp on lower side	Internal thread	PG 29
Number of cable entry on top	1	Number of cable entry sideways	0
Size	10	Size of cable entries	PG 29
Suitable for ModuPlug®	Yes	Tightening torque	2 Nm
Top part/bottom part/lid	upper part	Type	Plug

### Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant

Creation date March 6, 2023 10:53:30 AM CET

## HDC 32B TOBU 1PG29G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d447edfa-0214-4f34-b5ba-82eae491b46a
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@718c0e44 de.myview.objectmodel.impl.BlockImpl@2e4c3e02 de.myview.objectmodel.impl.BlockImpl@6b148e75 de.myview.objectmodel.impl.BlockImpl@297de183 de.myview.objectmodel.impl.BlockImpl@381234c6 de.myview.objectmodel.impl.BlockImpl@77e1b1e8 de.myview.objectmodel.impl.BlockImpl@3849ee47 de.myview.objectmodel.impl.BlockImpl@7efe6134 de.myview.objectmodel.impl.BlockImpl@5763ce29 de.myview.objectmodel.impl.BlockImpl@2df74bdc de.myview.objectmodel.impl.BlockImpl@5abba3f3 de.myview.objectmodel.impl.BlockImpl@57419e51 de.myview.objectmodel.impl.BlockImpl@1e9a0016

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Product Change Notification	<a href="#">20220214 Technical change to HDC housings</a> <a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a>
Technical Documentation	<a href="#">1666870000 HDC_32B_TOBU_1PG29G_STP_Blatt_1.pdf</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date March 6, 2023 10:53:30 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

3

**Data sheet**

**HDC 32B TOBU 1PG29G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

